

# PHILIPS

Soy milk maker

Viva Collection

1.0~1.2L

Boomerang blade

900W

Double housing

HD2061/02



## Enjoy smooth soymilk with ease and less effort

Easily prepare smooth soymilk with this Philips soymilk maker, featuring a twin boomerang-shaped blade. Thanks to the "Easy Clean" function and waterproof caps, fresh homemade soymilk is now available with less effort - to you & your family

### Better cutting performance

- Twin boomerang-shaped blade for finer cutting performance

### Easy cleaning

- Cageless design makes cleaning easier
- Dedicated "Easy Clean" button for increased convenience
- Enlarged bottom radius of inner pan allows for easy cleaning

### Easy filtering

- Finish filtering in one pour without stirring

### Safe to use

- Cover protects power connector for safer washing
- 100% food-grade lubricant on motor shaft seal & bearings

### Easy to use

- Four programs to enjoy your favorite drink easily

# Highlights

## Twin boomerang-shaped blade



The specially designed twin boomerang-shaped blade provides finer cutting performance. The two serrated wings bent down at different angles, which results in a more effective bean contact surface during cutting. Additionally, the two side wings improve bean distribution for optimal cutting performance.

## Cageless design




The cageless design and smooth surfaces without screws and protruding edges are easier to clean.

## "Easy Clean" button



Pressing the "Easy Clean" button starts preliminary cleaning by heating up and stirring the water, allowing for easy cleaning at your convenience with less effort.

## Enlarged bottom radius



The enlarged bottom radius of the inner pan allows for easy reach, so you can give it a clean sweep in one go.

## Specially designed sieve



Finish filtering in one pour without stirring thanks to the specially designed sieve.

## Power connection cover



This cover prevents water from entering the power connector, making washing safer.

## 100% food-grade lubricant



100% food-grade lubricant on motor shaft seal & bearings.

## Favorite drinks made easily



Making your favorite drink is easy by selecting the right program, including dry/soaked soymilk, five grains soymilk, rice paste & veggie/fruit juice.

# Specifications

## Accessories

Sieve  
Measuring cup

## Design specifications

Materials of outer housing: plastic  
Materials of inner housing: stainless steel  
Color(s): Star white and lavender  
Weight appliance: 2.39 kg

## Technical specifications

Capacity: 1.0~1.2 L  
Motor power: 150 W  
Heating power: 900 W  
Frequency: 50 Hz  
Voltage: 220 V

