

PHILIPS

Soy milk maker

Avance Collection

1.0~1.3L

Boomerang blade

900W

Double housing

HD2075



100% Safer, Healthier, Worry Free

Philips tailor-made soymilk maker HD2075/03 for Chinese consumers, using 100% food grade lubricant, with more-safe anti-splash caps, making using and cleansing more safe, so that frees you to enjoy fresh and smooth homemade soymilk.

Safe to use

- 100% food-grade lubricant on motor shaft seal & bearings
- Waterproof cap protects coupler for safer washing
- Cover protects power connector for safer washing

Easy cleaning

- Smooth surfaces are easier to clean
- Dedicated "Easy Clean" button for increased convenience
- Enlarged bottom radius of inner pan allows for easy cleaning

Easy filtering

- Finish filtering in one pour without stirring

Less residue, more milk

- Advanced cutting & grinding technology for less residue

Easy to use

- Six programs to enjoy your favorite drink easily

Highlights

100% food-grade lubricant



100% food-grade lubricant on motor shaft seal & bearings

"Easy Clean" button



Pressing the "Easy Clean" button starts preliminary cleaning by heating up and stirring the water, allowing for easy cleaning at your convenience with less effort

Specially designed sieve



Finish filtering in one pour without stirring thanks to the specially designed sieve

Waterproof cap at coupler



This waterproof cap prevents water from entering the coupler, which makes washing safer

Smooth surfaces



Smooth surfaces, without screws or protruding edges, are easier to clean

Advanced cutting & grinding




Advanced cutting & grinding technology significantly reduces residue and delivers more soymilk

Power connection cover



This cover prevents water from entering the power connector, making washing safer

Enlarged bottom radius



The enlarged bottom radius of the inner pan allows for easy reach, so you can give it a clean sweep in one go.

Favorite drinks made easily



Making your favorite drink is easy by selecting the right program, including dry/soaked soymilk, five grains soymilk, rice paste, veggie/fruit juice, vegetable puree soup & corn juice

Specifications

Accessories

Sieve
Measuring cup
Soymilk cup
Cleaning pad

Design specifications

Materials of outer housing: plastic
Materials of inner housing: stainless steel
Color(s): Start white and ink black
Weight appliance: 2.64 kg

Technical specifications

Capacity: 1-1.3 l
Voltage: 220 V
Frequency: 50 Hz
Motor power: 180 W
Heating power: 900 W

