

PHILIPS

Soy milk and
SoupMaker

Avance Collection

1.0~1.3L

Boomerang blade

900W

Double housing

HD2078/02



Safer, Healthier & Worry Free

Next to 100% food-grade lubricant, this upgraded Philips soymilk maker now features cageless cutting technology and a twin boomerang-shaped blade for easier cleaning & finer cutting. Enjoy fresh & smooth homemade soymilk with your family!

Safe to use

- 100% food-grade lubricant on motor shaft seal & bearings
- Cover protects power connector for safer washing
- Waterproof cap protects coupler for safer washing

Better cutting performance

- Twin boomerang-shaped blade for finer cutting performance

Easy cleaning

- Cageless design makes cleaning easier
- Dedicated "Easy Clean" button for increased convenience
- Enlarged bottom radius of inner pan allows for easy cleaning

Easy filtering

- Finish filtering in one pour without stirring

Easy to use

- Six programs to enjoy your favorite drink easily

Highlights

100% food-grade lubricant



100% food-grade lubricant on motor shaft seal & bearings

Waterproof cap at coupler



This waterproof cap prevents water from entering the coupler, which makes washing safer

Power connection cover



This cover prevents water from entering the power connector, making washing safer

Twin boomerang-shaped blade



The specially designed twin boomerang-shaped blade provides finer cutting performance. The two serrated wings bent down at different angles, which results in a more effective bean contact surface during cutting. Additionally, the two side wings improve bean distribution for optimal cutting performance.

Cageless design




The cageless design and smooth surfaces without screws and protruding edges are easier to clean

"Easy Clean" button




Pressing the "Easy Clean" button starts preliminary cleaning by heating up and stirring the water, allowing for easy cleaning at your convenience with less effort

Enlarged bottom radius



The enlarged bottom radius of the inner pan allows for easy reach, so you can give it a clean sweep in one go.

Specially designed sieve



Finish filtering in one pour without stirring thanks to the specially designed sieve

Favorite drinks made easily



Making your favorite drink is easy by selecting the right program, including dry/soaked soymilk, five grains soymilk, rice paste, veggie/fruit juice, vegetable puree soup & corn juice

Specifications

Accessories

Sieve
Measuring cup
Soymilk cup
Cleaning pad

Design specifications

Materials of outer housing: plastic
Materials of inner housing: stainless steel
Color(s): Star white and grey
Weight appliance: 2.58 kg

Technical specifications

Capacity: 1-1.3 L
Voltage: 220 V
Frequency: 50 Hz
Motor power: 150 W
Heating power: 900 W

