

# PHILIPS

Soy milk maker

Avance Collection

0.9~1.1L

5 programs

850 W

No need to filter

HD2079/08



## Consume the whole bean for full nutritional value

Drink directly, no need to filter

Want to enjoy more nutrition from beans? Too busy to filter in morning? Thanks to PowerGrind & Super steam heating technology of Philips Filter-free Soymilk maker, you can now enjoy whole bean nutrition and rich taste. No more filtering!

### **Whole Bean Nutrition, 20% more protein**

- PowerGrind technology cuts beans finely, no filtering
- Super steam heating technology improves the soymilk taste

### **Multifunction**

- 5 programs and well designed recipe book

### **Easy to use & clean**

- Rotating lid design makes lifting safer & more convenient
- Non-discoloring stainless steel hood for easy cleaning
- Low noise

### **Safe to use**

- Double stainless housing, keeps warm, prevent scalding
- 100% food grade oil

# Highlights

## PowerGrind technology



Advanced PowerGrind technology cuts beans more finely, so there's no need for filtering! What's more, 20% more dissolved protein is extracted from the soybeans\* (\* tested by Philips, compared with Philips HD2072/01)

## Super steam heating technology



Super saturated steam heating technology stabilizes the temperature inside the pot, facilitating the transformation from soybean to soy milk and improving the soy milk taste.

## Favourite drinks made easily



Making your favorite drink is easy by selecting the right program, including soy milk, rice paste, pureed soup, chunky soup and fruit/veggie juice.

## Rotating lid




Rotating lid design protects against leaking when dropped, making lifting safer and more convenient.

## Stainless steel hood



Non-discoloring stainless steel hood for easy cleaning.

## Double stainless housing



Double stainless housing, keeps warm, prevent scalding.

## Low noise



Low noise

## 100% food grade oil



100% food grade oil

# Specifications

## Design specifications

Materials of outer housing: Stainless steel

Materials of inner housing: Stainless steel

Weight appliance: 2 kg

## Technical specifications

Capacity: 1.1 L

Voltage: 220 V

Frequency: 50 Hz

Motor power: 140 W

Heating power: 850 W

## Weight and dimensions

F-box dimensions: 230 x 230 x 340.5 mm

F-box weight: 2.5 kg

