

PHILIPS

All-In-One Cooker

Viva Collection

16 Pre-set menus

Non-stick inner pot

6L, 1000W

HD2137



The All-in-One Solution for your cooking needs Fully customized cooking style and time

With intelligent cooking system, you can slow cook, pressure cook and multi cook all in the one machine.

Smart and various cooking

- Slow cook with high & low temperature up to 12 hours
- Sauté/Sear with high & low temperature
- Pressure cook with various direct menu buttons
- Multi cook menus with recommended cooking time
- Automatic keep warm for 12 hours, reheat functions

Easy to operate

- Easy to control cooking progress
- Easy to program timer indicates the cooking progress

The ultimate in convenience

- Durable and non-stick inner pot
- Easy-to-clean detachable inner lid design

Safe cooking

- Auto pressure release to ensure safety
- 9 safety protection systems

Highlights

Safety auto pressure release

In case of abnormal high pressure inside the cooker, steam will be released automatically from the pressure regulator valve to ensure safety.

Durable & non-stick inner pot



Aluminum alloy inner pot is durable and offers more effective heat conduction. Special colored Whitford golden coating is anti-scratch and non-stick.

Easy to program timer



Easy to program timer indicates the cooking progress

Multi cook menus

Multi cook menus (Yogurt, stew, bake) with recommended cooking time.

Pressure cook menus



Pressure cook with various direct menu buttons (Soup, Risotto, Rice, Steam, Meat/Poultry, Manual)

Saute/Sear with high/ low temp

Saute/Sear with high & low temperature up to 2 hours



Slow cook with high & low temperature up to 12 hours

Easy-to-clean



Easy-to-clean detachable inner lid design.

Specifications

Accessories

Cookbook
Ladle
Measuring cup
Spatula
Plastic steam tray

Packaging dimensions

Number of products included: 1
Packaging type: Display

Design specifications

Color of control panel: Black
Color(s): Silver
Materials of main body: Stainless steel

Technical specifications

Capacity: 6 Litres / cups
Cord length: 1.2 m
Wattage: 1000 W