

# PHILIPS

## Toaster

Daily Collection

8 settings

Integrated bun warming rack

Compact design

Dust cover



HD2582/00



## Crispy golden brown toast every day

With 8 settings and integrated bun warming rack

This compact toaster comes with 8 settings and 2 large variable slots, so you can have even toasting result regardless of different bread types. The integrated bun rack also allows you to warm your favorite buns, pastries and rolls easily.

### Even toasting results

- 8 browning settings for individual preference
- 2 large variable slots for different size of bread
- Integrated bun rack for heating rolls, pastries or buns

### Easy to use


- Reheat, defrost in one go
- Cancel button to stop toasting at any time
- Removable crumb tray for easy cleaning
- High lift to safely take out smaller pieces
- Extra auto shut-off protection



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## 8 browning settings



8 settings allow you to toast different types of bread without the risk of getting it burnt. Adjust the browning setting to your preference and get your toast the way you want it.

## 2 large variable slots



2 large variable slots for different size of bread. The bread is kept in the center for even browning results on both sides, thanks to the self-centering feature.

## Integrated bun rack



Integrated bun rack to warm your favorite buns, pastries and rolls easily.

## Reheat, defrost in one go



The reheat function warms toast in seconds, and the defrost function helps to toast frozen bread in one go.

## Stop anytime



Stop at any moment you like by pressing the stop button.

## Removable crumb tray



Easy to clean thanks to the removable crumb tray.

## High lift function



High lift feature to easily remove small pieces of bread.

## Extra auto shut-off protection



Extra auto-off protection protects the product against short circuit.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Accessories

Included: Dust cover

## Country of origin

Made in: China

## Design and finishing

Color(s): White

Material of main body: Plastic

## General specifications

Number of browning levels: 8

Product features: Adjustable browning, Automatic shut-off, Cancel button, Cool wall exterior, Defrost function, High lift function, Integrated cord storage

## Service

2-year worldwide guarantee

## Sustainability

User manual: 100% recycled paper

## Technical specifications

Frequency: 50-60 Hz

Power: 760-900 W

Voltage: 220-240 V

## Weight and dimensions

Dimensions of packaging (LxWxH):

304x184x214 mm

