

PHILIPS

Toaster

Daily Collection

Long slot

3 function

Black & misty blue

XL slot, bun warmer, cool wall

HD2611/61



Enjoy great toast

Toaster with XL slot to fit all types of bread

Philips toaster with XL slot and variable width feature to ensure evenly golden brown toast. Ideal for baguettes, bagels and big bread slices. Features integrated bun warming rack, slide out crumb tray, reheat and frozen bread function.

The way you want it

- Bun warming rack to warm buns and croissants
- Extra long slots to fit all kinds of bread
- Extrawide slots to fit your bread, thick or thin

Easy to experience

- Defrost and toast frozen bread at any browning level
- Reheat function in browning control
- Removable crumb tray for easy cleaning

With maximum safety

- Automatic safety shut-off in event of jammed bread
- The outside of the toaster stays cool and safe to touch
- High lift feature to safely take out small pieces of bread
- Cancel button to stop toasting at any time

Highlights

Removable crumb tray

Is easy to clean thanks to its removable crumb tray.

Coolwall exterior



The outside of the toaster stays cool and safe to touch.

High lift feature

High lift feature to safely take out small pieces of bread.

Cancel button



Cancel button to stop toasting at any time

Extrawide slots

Philips toaster with extra wide slots to fit your bread, thick or thin.

Frozen bread function



Defrost and toast frozen bread at any browning level

Automatic safety shut-off

The toaster will automatically shut-off if the bread gets jammed inside.

Bun warming rack



Bun warming rack to warm buns and croissants.

Extra long slots



With extra long slots you can fit various kinds of bread including baguettes, or put two or more smaller slices at a time.

Reheat function



Set the browning control to reheat in order to warm cold bread or further browns just toasted bread.

Specifications

Design specifications

Materials: Plastic housing (PP/PC/ABS), chrome plated top

Color(s): Black and misty blue

General specifications

Cord storage

Non slip feet

Automatic safety shut-off

Technical specifications

Power: 1200 W

Voltage: 220-240 V

Cord length: 0.85 m

