

# PHILIPS

## Toaster

2 slot

3 function

Gloss metal

HD2626/22



## Enjoy great toast

Thick or thin, always golden brown

Toaster with variable width slots and browning control to have great toast your way. Evenly golden brown, thick or thin. Convenient due to defrost and reheat function. Safe to use thanks to high lift feature and cool wall exterior.

### Enjoy great toast

- Evenly toasts thick or thin slices

### Easy to experience

- Removable crumb tray for easy cleaning
- High lift feature to easily remove small pieces of bread

### Safe to use

- The outside of the toaster stays cool and safe to touch
- Cancel button stops toasting at any time
- The outside of the toaster stays cool and safe to touch

# Highlights

## Variable width bread slots

Evenly toasts thick or thin slices.

## Removable crumb tray

Is easy to clean thanks to its removable crumb tray.

# Specifications

## Design specifications

**Colour(s):** Black/Metal gloss

## General specifications

Cord storage

Non-slip feet

Automatic safety shut-off

## Technical specifications

**Power:** 1000 W

**Voltage:** 220-240 V

**Frequency:** 50-60 Hz

**Cord length:** 0.85 m

**Slot size (L x W x H):** 136 x 32 x 131 mm

