

PHILIPS

Toaster

Viva Collection

2 slot

3 function

Oyster metallic

Extra wide slot, bun warmer

HD2630/50



Enjoy great toast

Toaster for always golden brown bread

Philips Toaster with wide deep slots and self-centering feature to ensure evenly golden brown toast on thick or thin slices. Features integrated bun warming rack, slide out crumb tray and one-touch reheat and defrost buttons.

The way you want it

- Extrawide slots to fit your bread, thick or thin
- Bun warming rack to warm buns and croissants
- Variable width self-centered slots for evenly toasted bread

Easy to experience

- Defrost or reheat just toasted bread in one go
- Removable crumb tray for easy cleaning

With maximum safety

- High lift feature to safely take out small pieces of bread
- The outside of the toaster stays cool and safe to touch
- Automatic safety shut-off in event of jammed bread
- Cancel button to stop toasting at any time

Highlights

Bun warming rack




Bun warming rack to warm buns and croissants.

Removable crumb tray



Is easy to clean thanks to its removable crumb tray.

Extrawide slots



Philips toaster with extra wide slots to fit your bread, thick or thin.

Wide self-centered slots



Philips toaster with self-centered slots allow you to put thick or thin slices and make sure they stay in the center for evenly toasted bread.

High lift feature



High lift feature to safely take out small pieces of bread.

Specifications

Design specifications

Materials: Plastic housing (PP/PC/ABS), chrome plated top
Color(s): White/lavender

General specifications

Cord storage
Non slip feet
Automatic safety shut-off

Technical specifications

Power: 850-1000 W
Voltage: 220-240 V
Cord length: 0.85 m

