

PHILIPS

Toaster

Viva Collection

2 slot

3 function

Bun warmer

HD2636/20



Enjoy great toast

Toaster for always golden brown bread

Philips toaster HD2636/20 with wide deep slots and self-centering feature to ensure evenly golden brown toast on thick or thin slices. Features integrated bun warming rack, slide out crumb tray and one-touch reheat and defrost buttons.

The way you want it

- Bun warming rack to warm buns and croissants
- Variable width self-centered slots for evenly toasted bread
- Extrawide slots to fit your bread, thick or thin
- Adjustable seven levels of browning control

Easy to experience

- Removable crumb tray for easy cleaning
- Cord winding facility for easy storage
- Reheat, defrost and toast frozen bread at any browning level

With maximum safety

- Automatic safety shut-off in event of jammed bread
- The outside of the toaster stays cool and safe to touch
- High lift feature to safely take out smaller pieces
- Cancel button to stop toasting at any time

Highlights

Coolwall exterior



The outside of the toaster stays cool and safe to touch.

Cancel button



Cancel button to stop toasting at any time

Extrawide slots



Philips toaster with extra wide slots to fit your bread, thick or thin.

Removable crumb tray



Is easy to clean thanks to its removable crumb tray.

Automatic safety shut-off

The toaster will automatically shut-off if the bread gets jammed inside.

Bun warming rack



Bun warming rack to warm buns and croissants.

High lift feature



This feature allows you to lift smaller pieces of bread even higher to take them out safely.

Wide self-centered slots

Philips toaster with self-centered slots allow you to put thick or thin slices and make sure they stay in the center for evenly toasted bread.

Seven adjustable levels



The Philips Avance Collection Toaster has seven adjustable levels of browning control.

Cord winding facility

Cord winding facility for easy storage

Reheat, defrost and toast froz



Reheat, defrost and toast frozen bread at any browning level

Specifications

Accessories included

Bun warmer

Design specifications

Materials: Brush stainless-steel housing,

Chrome plated top

Color(s): Silver metal, black

General specifications

Cord storage

Non slip feet

Technical specifications

Power: 850-1000 W

Slot size (L x W x H): 130 x 32 x 120 mm

Cord length: 0.85 m

Voltage: 220 - 240 V

Frequency: 50 - 60 Hz

