

# PHILIPS

## Toaster

Viva Collection

2 slot

3 function

Black silver

HD2636/20



## Enjoy great toast

Thick or thin, always golden brown

Philips toaster HD2636/20 with wide, deep slots and self-centring feature to ensure evenly golden brown toast on thick or thin slices. Features integrated bun warming rack, slide-out crumb tray and one-touch reheat and defrost buttons.

### The way you want it

- Bun warming rack to warm buns and croissants
- Variable width self-centred slots for evenly toasted bread
- Extra wide slots to fit your bread, thick or thin
- Adjustable seven levels of browning control

### Easy to experience

- Removable crumb tray for easy cleaning
- Cord winding facility for easy storage
- Reheat, defrost and toast frozen bread at any browning level

### With maximum safety

- Automatic safety shut-off in the event of jammed bread
- The outside of the toaster stays cool and safe to touch
- High lift feature to safely take out smaller pieces
- Cancel button stops toasting at any time

# Highlights

## Cool wall exterior



The outside of the toaster stays cool and safe to touch.

## Cancel button



Cancel button stops toasting at any time

## Extra wide slots



Extra wide slots to fit your bread, thick or thin.

## Removable crumb tray



Is easy to clean thanks to its removable crumb tray.

## Automatic safety shut-off

The toaster will automatically shut off if the bread gets jammed inside.

## Bun warming rack



Bun warming rack to warm buns and croissants.

## High lift feature



This feature allows you to lift smaller pieces of bread even higher to take them out safely.

## Wide self-centred slots

The self-centred slots allow you to use thick or thin slices and make sure they stay in the centre for evenly toasted bread.

## Seven adjustable levels



The Philips Avance Collection Toaster has seven adjustable levels of browning control.

## Cord winding facility

Cord winding facility for easy storage

## Reheat, defrost and toast froz



Reheat, defrost and toast frozen bread at any browning level

# Specifications

## Accessories included

Pastry warmer

## Design specifications

Materials: Brushed stainless steel housing,

Chrome-plated top

Colour(s): Silver metal, black

## General specifications

Cord storage

Non-slip feet

## Technical specifications

Power: 850-1000 W

Slot size (L x W x H): 130 x 32 x 120 mm

Cord length: 0.85 m

Voltage: 220 - 240 V

Frequency: 50 - 60 Hz

