

PHILIPS

Toaster

Viva Collection

Extra wide 2 slots toaster

Built in bun warmer

Black

HD2637/90



Great Crispy toast no matter hand cut or pre-slice

Extra wide slots catering easily thick or thin

10% Wider slots size* together with the self centering racks, regardless thin slices or thick hand cut slices, always hold and lock each slice perfectly centered for even browning result.

Easy to control

- Adjustable 7 levels of browning control
- Reheat, defrost in one go

Easy to experience

- Extra wide slot fits thick or thin, fresh or frozen slices.
- Built in bun rack for heating rolls, pastries or buns
- Removable crumb tray for easy cleaning

With maximum safety

- Extra auto shut-off protection
- High lift to safely take out smaller pieces
- Cancel button to stop toasting at any time

Highlights

Extra wide slot



The self centering mechanism perfectly centers each slice for even browning, regardless of thickness.

7 adjustable browning levels

Adjust the heat level to your preference and get your toast the way you want it.

High lift to safely take out



The feature allows you to lift smaller pieces of bread safely

Built-in Bun rack



Built in bun rack to warm pastries, rolls or buns easily.

Reheat, defrost in one go



Reheat and defrost functions to toast frozen toast/bread in one go

Cancel button to stop toasting



Stop button to stop toasting at any time

Removable crumb tray



Easy to clean thanks to the removable crumb tray.

Extra auto-off protection



Extra auto-off protection protects the product against short circuit.

Specifications

Country of origin

Made in: China

Design and finishing

Color(s): Black

Material of main body: Metal & Plastic

General specifications

Number of browning levels: 7

Product features: Adjustable browning, Automatic shut-off, Cancel button, Cord storage, Defrost function, High lift function, Non-slip feet

Service

2-year worldwide guarantee

Sustainability

User manual: 100% recycled paper

Technical specifications

Cord length: 0.85 m

Frequency: 50-60 Hz

Voltage: 240 V

Weight and dimensions

Dimensions of packaging (LxWxH):

334x200x221 mm

Dimensions of product (LxWxH):

300x172x201 mm

Slot size (LxWxH): 138x33x125 mm

Weight incl. packaging: 1.95 kg

Weight of product: 1.49 kg

