

# PHILIPS

## Toaster

Pure Essentials  
Collection

2 slot

3 function electronic

White

Extra long slot

HD2686/39



### Have it your way, exactly your way Toasts any type of bread you like

State-of-the art toaster that enables you to prepare exactly the kind of toast you want, thanks to the extra long, extra wide slots. The eight digital browning settings give you full control so you get the crispy toasted bread you like.

#### **Toast any type of bread**

- Extrawide and extradeep slot(s) to fit your bread
- Evenly toasts thick or thin slices
- Extralong slots to fit all kinds of bread

#### **Exactly the way you like**

- Bun warming rack to warm buns and croissants
- Defrost and toast frozen bread at any browning level
- Reheat setting warms or further browns just toasted bread

#### **In the easiest way**

- Removable crumb tray for easy cleaning
- High lift feature to safely take out small pieces of bread
- Cancel button to stop toasting at any time
- The outside of the toaster stays cool and safe to touch

# Highlights

## Extrawide and extradepth slot(s)

Extrawide and extradepth slot(s) to fit your bread.

## Variable width bread slots

Evenly toasts thick or thin slices.

## Bun warming rack



Bun warming rack to warm buns and croissants.

## Removable crumb tray

Is easy to clean thanks to its removable crumb tray.

# Specifications

## Design specifications

**Materials:** Housing: metal/plastic (PC/ABS), chrome plated top

**Color(s):** White/Metal/red with DC

## General specifications

**Automatic safety shut-off**

**Multiple toast settings:** 8

## Technical specifications

**Power:** 1500 W

**Voltage:** 220-240 V

**Frequency:** 50/60 Hz

**Cord length:** 0.85 m

**Slot size (L x W x H):** 152X30X130 mm