

# PHILIPS

## Toaster

Pure Essentials  
Collection

2 slot

3 function electronic

Black

Extra-long slot



HD2686/90



## Have it your way, exactly your way

### Toaster for different types of bread

This Philips toaster HD2686/90 enables you to prepare the kind of toast you want, thanks to the extra-long, extra-wide slots. The eight digital browning settings give you full control so you get the crispy toasted bread you like.

#### **Toast any type of bread**

- Extra long slots to fit all kinds of bread
- Extra wide and extra deep slot(s) to fit your bread
- Evenly toasts thick or thin slices

#### **Exactly the way you like**

- Bun warming rack to warm buns and croissants
- Defrost and toast frozen bread at any browning level
- Reheat setting warms or further browns just-toasted bread

#### **In the easiest way**

- Cancel button stops toasting at any time
- High lift feature to safely take out small pieces of bread
- The outside of the toaster stays cool and safe to touch

# Highlights

## Extra long slots

Extra long slots to fit all kinds of bread.

## Extra wide and extra deep slot(s)

Extra wide and extra deep slot(s) to fit your bread.

## Variable width bread slots



Evenly toasts thick or thin slices.

## Bun warming rack



Bun warming rack to warm buns and croissants.

## Frozen bread function



Defrost and toast frozen bread at any browning level

## Reheat setting

Reheat setting warms or further browns just-toasted bread

## Cancel button



Cancel button stops toasting at any time

## High lift feature



High lift feature to safely take out small pieces of bread.

## Cool wall exterior

The outside of the toaster stays cool and safe to touch

# Specifications

## General specifications

Multiple toast settings: 8  
Automatic safety shut-off

## Technical specifications

Power: 1500 W  
Slot size (L x W x H): 152 x 30 x 130 mm  
Cord length: 0.85 m  
Voltage: 220-240 V  
Frequency: 50/60 Hz

## Design specifications

Materials: Housing: metal/plastic (PC/ABS), chrome-plated top  
Colour(s): Black, metal and red

