

PHILIPS

Fuzzy Logic Rice
Cooker

Avance Collection

Fuzzy logic

1.0 liter

6 cups

HD3030/62



Freshness locked in, your best rice every time

Smart automatic cooking program for optimal result

Nutrition is important to keep healthy. Philips' new multicookers come with smart cooking programs on temperature control so that freshness and nutrition is better preserved. Top front control panel for easier operation.

Smart and automatic cooking

- Fuzzy Logic control for fresh and nutritious meals
- Nutritional Keep warm keeps rice fresh for 12 hours
- Reheat function for fresh rice instantly
- 24 hours preset timer ensures meals are ready on time
- Unique 6 steps smart cooking program
- Backup memory when power interruption

3 different healthy varieties


- 1.5mm 5-layer inner pot for even heating, cooks rice tastier
- 3 food menu for more healthy varieties.

The ultimate in convenience

- Swing handle for easy carrying
- Detachable steam vent for easy cleaning
- 6F technology for self-protecting & prolonging life time
- Clear vision with extra large digital display panel

Highlights

1.5mm 5-layer inner pot



1.5mm 5-layer inner pot for even heating, cooks rice tastier.

Clear vision

Clear vision with extra large digital display panel

Automatic 12 hours keep warm



Use the keep warm function to keep rice or dishes warm for a longer period of time, without losing food nutrition and taste. When the cooking process is finished, the rice cooker automatically switches to the keep warm mode

Specifications

General specifications

Smart & automatic programs for optimal end result*

Reheat function for: fresh rice instantly

Easy-to-clean non-stick inner pot

Dish washer safe inner pot

Swing handle for easy carrying

Spillover prevention vent

Backup memory when power interruption

Easy-to-program timer

Design specifications

Color of control panel: Silver

Materials of main body: PP

Color(s): White

Dimensions (L x W x H): 377X245X210 mm

Weight (incl. packaging): 3.0 kg

Accessories

Plastic steam tray

Rice scoop

Soup scoop

Measuring cup

Technical specifications

Voltage: 220-240 V

Frequency: 50-60 Hz

Wattage: 600 W

Cord length: 1.2 m

Inner pot capacity: 3L

Capacity: 1.0 Litres / cups

