

# PHILIPS

Philips Digital Rice Cooker

Viva Collection

4 cooking menus

ProCeramic+ Inner Pot

48hr keep warm

Big capacity of 2L

HD3053



## Cooks white and brown rice perfectly

With fuzzy logic tech and long lasting Proceramic+

Innovative built-in processor to smartly monitor the heat and temperatures to ensure white and brown rice comes out to perfection every time. Inner pot is up to 5 times more durable, its super scratch resist surface is for longer usage.

### Smart and automatic cooking

- Fuzzy logic control for fresh and nutritious meals
- Automatic keep warm function for up to 48 hours
- Smart 3D heating system cooks rice evenly

### The ultimate in convenience

- Extra large 2.0L capacity serves up to 14 people
- Easy to remove inner pot thanks to stay cool handles
- Fully detachable inner lid for easy cleaning

### Strong and durable design

- Durable stainless steel body for long lasting performance

### Long lasting ProCeramic+ pot

- High gloss non-stick coating for easy cleaning
- Outer layer contains copper element for even cooking
- State of the art ProCeramic+ coating is 5 times more durable

# Highlights

## Evenly cooking

Outer layer contains copper element for even cooking

## Extra Large capacity



Extra large 2.0L capacity, ideal to serve up to 14 people

## Fuzzy logic technology

Innovative temperature processor to smartly monitor the heat settings and temperatures of device to ensure white rice and brown rice comes out to perfection every time. It also offers you the ability to cook congee and baking with versatility cooking programs.

## Automatic keep warm

Automatic keep warm function for up to 48 hours

## Smart 3D heating system



Smart 3D heating system cooks the rice from all directions, delivering great tasting rice grain by grain

## ProCeramic+ coating

ProCeramic plus: up to 5 times more durable than conventional rice cooker\*. Its super scratch resistant surface is for longer usage (\*Philips rice cooker inner pot is made of 5-layer ProCeramic+ and conventional rice cooker inner pot is made of non-stick coating).

## Stainless steel body

Durable stainless steel body for long lasting performance

## Easy to remove inner pot

Easy to remove inner pot thanks to the specially designed stay cool handles.

## Fully detachable inner lid

Fully detachable inner lid for easy cleaning. The inner lid also encompasses a unique design that can efficiently remove foam and prevent overflow during cooking

## High gloss non-stick coating

High gloss non-stick coating for easy cleaning

# Specifications

## Accessories

Included: Measuring cup, Spatula, Steaming tray/basket

## Country of origin

Made in: China

## General specifications

Keep warm function: 48 hour(s)

## Service

2-year worldwide guarantee

## Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

## Technical specifications

Cord length: 0.8 m

Frequency: 50 Hz

Voltage: 230 V

Power: 912 W

Inner pot capacity: 6L

Working capacity bowl: 1.8 L

## Design

Color: Gold

## Finishing

Material of main body: Metal

