

# PHILIPS

## Rice Cooker

### Viva Collection

#### Mini-cooker

0.7 L

330W

HD3060



## Small size, big functionality

### Various menus to meet different cooking needs

The creative Philips mini-cooker with various menus is the perfect size to create multiple healthy recipes for fresh meals every time.

#### **Comprehensive functions with stunning performance**

- Hydrating micro-pressure design for outstanding performance
- Five major cooking functions
- Includes: rice, soups, congee, stews, yogurt and risottos

#### **Easy cleaning**

- Detachable inner lid for easy cleaning

#### **Provides delicious food in perfect portions**

- 0.7L volume designed for single people or small families
- Compact design takes up a small amount of space

#### **Stylish and eye-catching**

- Touch sensor for easy operation

# Highlights

## 0.7L rice capacity

0.7L volume holds 4 cups of rice and congee made with 0.5 cups of rice. Suitable for single people or small families, with no need to worry about leftovers

## 5 major functions



Select reheating and warming functions with one touch for hot food whenever you want it; The cooking completion times for all 6 menus can be set 24 hours in advance. Finish your breakfast or dinner early for a hassle-free life; Cooking times can be adjusted as necessary. Cooking times for soups, congee and stews can be adjusted between 1-4 hours, and yogurt between 4-12 hours; Also comes with a child lock function giving you peace of mind

## 6 menus

Six handpicked menus: Rice, risottos, soups and congee for all your daily needs; Nourishing stews and yogurt provide the nutrition you need for a healthy life.

## Compact design



Compact design takes up a small amount of space.

## Detachable inner lid



Aluminum alloy inner lid can be detached and cleaned to prevent the buildup of dirt and bacteria

## Hydrating micro-pressure valve

Built-in hydrating micro-pressure valve design provides maximum moisture retention, bringing out the natural flavor of the food for optimum taste

# Specifications

## Accessories

Measuring cup  
Rice scoop  
Soup scoop

## Technical specifications

Cord length: 1 m  
Frequency: 60 Hz  
Voltage: 230 V  
Wattage: 330 W  
Inner pot capacity: 2 L  
Rice capacity: 0.7 L

## Design specifications

Dimensions (L x W x H): 395\*300\*245 mm  
Color(s): Black and blue

