

PHILIPS

Fuzzy Logic Rice
Cooker

Advance

4L

8 cups

HD3065/52



Tastier Rice, Enjoyable Meal

Cooking in the style of the traditional big pot

The Philips cooker looks great with a 4 digital display, temperature control and an extremely durable, cutting-edge 5-layer golden inner pot, which conducts heat evenly for food cooked in the traditional Chinese style of the big pot.

Smart and automatic cooking

- Smart heating and temperature control for optimum results
- 24-hour preset timer ensures rice and meal ready on time
- The Keep-warm function keeps rice fresh for up to 12 hours

Easy to operate

- Easy-to-control touch sensor. Waterproof and durable panel.

Nine different healthy varieties

- Nine food menus for more healthy varieties

Outstanding design + Premium material

- Child lock keeps your kitchen safer and offers peace of mind
- Tasteful champagne-colored appearance
- Specially-designed accessories
- Extra-thick, non-stick easy to clean, 2.0-mm pot.

Highlights

24-hour preset timer



There is also a timer function to preset when you want the meal cooked. Press the 'hour' button once to advance 1 hour, and the 'minute' button to advance 10 minutes. The timer function can be preset up to 24 hours in advance to ensure you can enjoy your meals exactly when you want them.

Child lock



You can lock the control panel by pressing down on the 'Child lock' button for three seconds. This automatically locks the operation panel, ensuring there is no misuse from children during the cooking procedure. Press the 'Child lock' button for another 3 seconds to unlock it.

Nine food menus



There are nine selected cooking menu varieties including Quick cook, Ultra-quick cook, Small portions of rice, Reheating,

Congee/Soup, rice soup, Cakes and Clay pot rice. The intelligent cooking process enables you to cook great tasting rice with ease.

Sensor touch system



The control system uses an innovative, high-tech sensor touch feature. This avoids mechanic damage to buttons that can occur with traditional push-button operation. It is waterproof and easy to clean, and stays touch-sensitive and precise.

Thick 2.0-mm 5-layer inner pot



The specially-designed inner pot offers more effective heat conduction. It brings you the traditional "big pot" taste. The cutting-edge extra-thick 2.0-mm, 5-layer golden inner pot ensures even heating. 1. The super-rigid crystal coating is non-stick and anti-scratch, making it easy to clean and highly durable; 2. The rose-gold base effectively increases the heat during cooking; 3. The extra-thick alloy pot conducts heat evenly; 4. The resin coating protects the alloy and makes the pot firmer and more durable; 5. The black outer coating helps to retain heat and keeps your rice warm and fresh.

Specifications

General specifications

4 rice menu
5 cooking menu
12 hours keep warm
Swing handle for easy carrying
Spillover prevention vent

Design specifications

Materials of main body: SUS430
Color(s): Champagne
Color of control panel: Champagne

Accessories

Plastic steam tray
Measuring cup
Soup scoop
Spatula

Technical specifications

Voltage: 220 V
Frequency: 50 Hz
Wattage: 860 W
Cord length: 1.0 m
Capacity: 4/8 Litres / cups

