

PHILIPS

Fuzzy Logic Rice
Cooker

Advance

1.5 liter

HD3085/52



Tastier Rice, Enjoyable Meal

Cooking in the style of the traditional big pot

The Philips cooker looks great with a large LCD display, temperature control and an extremely durable, cutting-edge 5-layer golden inner pot, which conducts heat evenly for food cooked in the traditional Chinese style of the big pot.

Smart and automatic cooking

- 24-hour preset timer ensures rice and meal ready on time
- The Keep-warm function keeps rice fresh for up to 12 hours

Eleven different healthy varieties

- Eleven food menus for more healthy varieties
- 3D heating for even heating and more effective warm keeping

Outstanding design + Premium material

- 6.0-mm inner pot brings you the traditional "big pot" taste
- Child lock keeps your kitchen safer and offers peace of mind
- Easy to clean detachable inner lid

Easy to operate

- Sensitive sensor touch operational panel
- Easy-to-program timer ensures rice and meal is ready on time

Highlights

24-hour preset timer



There is also a timer function to preset when you want the meal cooked. Press the 'hour' button once to advance 1 hour, and the 'minute' button to advance 10 minutes. The timer function can be preset up to 24 hours in advance to ensure you can enjoy your meals exactly when you want them.

3D heating system



There is heating system surround the rice cooker, including heater assembly on the top, heater assembly all around and main heater

assembly on the bottom. 3D heating system for even heating, more effective warm keeping and better baking result

6.0-mm 5-layer inner pot



The thickness of inner pot gradually changes from 6.0 mm on the bottom to 2.0 mm on the top. It can conduct the heat generated from the main heater assembly on the bottom evenly to the top of the inner pot. 5-layer golden inner pot offers more effective and even heat conduction

Easy to clean detachable inner lid



Easy to clean detachable inner lid

Specifications

Accessories

Spatula
Soup scoop
Plastic steam tray
Measuring cup

Design specifications

Materials of main body: Plastic
Color(s): White
Color of control panel: Golden
Dimensions (L x W x H): 270x370x255 mm

Technical specifications

Capacity: 1.5/8 Litres / cups
Cord length: 1.0 m
Voltage: 220 V
Frequency: 50 Hz
Wattage: 980 W

General specifications

3 rice taste selection
9 rice menus
Artificial Intelligence control
Backup memory when power interruption
Detachable and washable inner lid
Detachable power cord for convenient storage
Dish washer safe inner pot
Durable, extra thick inner pot ensures even result
Easy-to-clean non stick inner pot
Large LCD with clock and timer display
Multi-menu selections*
Nutritional keep warm keeps rice fresh for 12 hrs
Spillover prevention vent
Swing handle for easy carrying
Timer mode ensures: rice is ready when you want

