

PHILIPS

Jar Rice Cooker

Daily Collection

Golden Pot with big handle

Smart 3D heating

48hr keep warm

Big capacity of 2L

HD3118/32



Great tasting rice, for all the family

Long lasting 5-layer pot

Philips non-stick and anti-scratch 5-layer golden inner pot conducts and retains heat more evenly, delivering hot fluffy great tasting rice for up to 48 hours.

5-layer golden inner pot

- Advanced anti-scratch coating for a long lasting pot
- High gloss non-stick coating by Whitford for easy cleaning

Advanced cooking system

- Smart 3D heating system cooks rice evenly
- Automatic keep warm function for up to 48 hours
- Extra thick alloy ensures every grain is cooked perfectly

Designed for convenience

- Extra large 2.0L capacity serves up to 14 people
- Easy to remove inner pot thanks to stay cool handles

Highlights

5-layer golden pot



Black Outer Coating: helps to retain heat, keeping the rice warm and fresh 2. Protective Resin: protects the alloy making the pot firmer and more durable 3. Extra Thick Alloy: Evenly conducts heat to ensure that every single grain of rice is boiled and cooked throughout, giving you the desired texture 4. Champagne Gold Base: spreads the heat throughout the whole pot during cooking so the rice is fluffy and tastier 5. Super Rigid Crystal Coating: non-stick and anti-scratch for easy cleaning and enhanced durability

Non-stick coating

High gloss non-stick coating by Whitford for easy cleaning

Smart 3D heating system



Smart 3D heating system cooks the rice from all directions, delivering great tasting rice grain by grain

Automatic keep warm



Keep warm function automatically starts to work after rice is cooked and ensures your rice remains hot and fluffy for up to 48 hours

Extra thick alloy



Extra thick alloy ensures every grain is cooked perfectly

Extra Large capacity



Extra large 2.0L capacity, ideal to serve up to 14 people

Stay cool handles



Easy to remove inner pot thanks to the specially designed stay cool handles

Specifications

Accessories

Included: Measuring cup, Spatula, Steaming tray/basket

Country of origin

Made in: China

General specifications

Product features: On/off switch, Power-on light

Service

2-year worldwide guarantee

Sustainability

Packaging: > 90% recycled materials
User manual: 100% recycled paper

Technical specifications

Capacity jar: 2.0 L
Cord length: 0.8 m
Frequency: 50 Hz
Power: 400 W
Voltage: 220 V

Weight and dimensions

Dimensions of product (LxWxH): 338 x 285 x 242 mm

Weight incl. packaging: 4.0 kg

Weight of product: 3.8 kg

Design

Color: Primary red & Star white

Color of control panel: Star White

Finishing

Material accessories: Plastic

Material of main body: Plastic

