

PHILIPS

Jar Rice Cooker

Viva Collection

ProCeramic Pot with big handle

Smart 3D heating

48hr keep warm

Big capacity of 2L

HD3128/34



Cooks every grain of rice perfectly

With the ultimate, long lasting ProCeramic Pot

Philips state of the art 5-layer ProCeramic pot is 3x harder than normal coatings ensuring your pot lasts longer and thanks to the 3D heating system, every grain is well cooked for you and your family to enjoy for up to 48 hours

Long lasting ProCeramic pot

- State of the art ProCeramic coating is 3x harder
- High gloss non-stick coating by Whitford for easy cleaning

Every grain well cooked

- Smart 3D heating system cooks rice evenly
- Automatic keep warm function for up to 48 hours
- Extra thick alloy ensures every grain is cooked perfectly
- Black outer coating retain heat and keep rice warm and fresh

The ultimate in convenience

- Extra large 2.0L capacity serves up to 14 people
- Easy to remove inner pot thanks to stay cool handles
- Fully detachable inner lid for easy cleaning

Strong and durable design

- Durable stainless steel body for long lasting performance

Highlights

5-layer ProCeramic Pot



1. Black Outer Coating: helps to retain heat, keeping the rice warm and fresh 2. Protective Resin: protects the alloy making the pot firmer and more durable 3. Extra Thick Alloy: Evenly conducts heat to ensure that every single grain of rice is boiled and cooked throughout, giving you the desired texture 4. ProCeramic state of the art coating: 3 times harder than normal pot coatings.

Non-stick coating

High gloss non-stick coating by Whitford for easy cleaning

Smart 3D heating system



Smart 3D heating system cooks the rice from all directions, delivering great tasting rice grain by grain

Automatic keep warm



Keep warm function automatically starts to work after rice is cooked and ensures your rice remains hot and fluffy for up to 48 hours

Extra thick alloy



Extra thick alloy ensures every grain is cooked perfectly

Black outer coating

Black outer coating retain heat and keep rice warm and fresh

Extra Large capacity



Extra large 2.0L capacity, ideal to serve up to 14 people

Stay cool handles



Easy to remove inner pot thanks to the specially designed stay cool handles

Fully detachable inner lid



Fully detachable inner lid for easy cleaning. The inner lid also encompasses a unique design that can efficiently remove foam and prevent overflow during cooking

stainless steel body

Durable stainless steel body for long lasting performance

Specifications

Accessories

Included: Measuring cup, Scoop, Steaming tray/basket

Country of origin

Made in: China

General specifications

Product features: On/off switch, Power-on light

Service

2-year worldwide guarantee

Sustainability

User manual: 100% recycled paper

Technical specifications

Capacity bowl: 2 L

Capacity watertank: 6 L

Cord length: 0.8 m

Frequency: 50 Hz

Voltage: 220 V

Power: 400 W

Weight and dimensions

Dimensions of product (LxWxH): 388 x 285 x 242 mm

Weight incl. packaging: 4.0 kg

Weight of product: 3.8 kg

Design

Color: Black & silver

Color of control panel: Golden

Finishing

Material accessories: Plastic

Material of main body: Stainless steel

