

PHILIPS

Rice cooker

Avance Collection

IH Heating

Original "Blaze Pot"

Metallic Latte



HD3175/62



Great tasting rice with every grain well cooked With Patented "iSpiral IH" heating technology

Patented technology stepping out of traditional IH thanks to our leading IH structure and micro-processor form ultra-strong outside-in currents that enables every grain well cooked

Multiple innovations

- Six-degree sloping lid design for comfortable use
- Define personal preferences using "My favorites"
- Multi function for a variety choice
- Patented "Fragrance-retaining valve"

iSpiral IH heating technology

- Enabling every grain well cooked
- Leading IH structure and micro-processor to form ultra-strong

"Blaze pot" for better heat conduction

- Inner layers store full of heat and energy
- Copper coating enhances heat conductivity

Meet Rohs and SGS standard

- RoHS-compliant, European-standard inner lid

Highlights

Patented "iSpiral IH"



Leading IH structure and micro-processor to form ultra-stron

Leading IH structure

Enabling every grain well cooked

Special valve structure



A specially designed fragrance-retaining valve structure

"My favorites" function



Intelligently stores up to three common cooking programs, so you can select your favorite cooking program straight from "My favorites".

Six-degree angled design



Six-degree sloping design, allowing you to use the cooker from the most comfortable position.

10 menu for variety choice

Innovative design, 10 main menus

Original "Blaze Pot"



"Blaze pot" for better heat conduction

Copper coating design

Copper coating enhances heat conductivity. Even the rice in the middle of pot is heated evenly.

RoHS and SGS standard

RoHS-compliant, European-standard inner lid

Specifications

Accessories

Included: Measuring cup, Non-stick innerpot, Spatula, Steaming tray/basket

Country of origin

Made in: China

General specifications

Product features: LED display, Preset cooking function, Power-on light

Prefix programs: 10 menus

Sustainability

User manual: 100% recycled paper

Technical specifications

Capacity bowl: 4 L

Frequency: 50 Hz

Voltage: 220~240 V

Power: 1500 W

Weight and dimensions

Dimensions of product (LxWxH): 365 x 280 x 225 mm

Design

Color: Metallic Latte & Star White

Color of control panel: Metallic Latte

