

PHILIPS

Pure water on tap

Mineral+

HD3802



Pure water made easy

with Mineral+ filter

Compact and easy to install water purifier that gives you pure water by removing bacteria, harmful organic compounds and chlorine while adding minerals to the water, to ensure you have delicious healthy pure water.

Pure water

- Mineral+ filter removes bacteria and chlorine
- Granular activated coral releases minerals into your water

Made easy

- Quick Fit tap adapters for easy installation on your tap
- Hi-flow ensures maximum flow rate of 4 liters per minute
- 360° rotation arm provides you maximum working space

Highlights

Mineral+ filter

The Mineral+ filter is a multi-filtration system that removes impurities and odours for pure, safe and tasty drinking water. It consists of a hi-tech hollow-fibre membrane, which contains more than 600 billion micro-pores for the efficient removal of 99.99% of all bacteria, and a granular activated carbon which removes unpleasant chlorine, bad taste and odours. The filter also preserves existing and add extra minerals in the drinking water that are vital for human health.

Granular activated coral

Granular activated coral is added to the Mineral+ filter to release minerals into your water that gives you a better taste water and improves your health and well being.

Quick Fit tap adapters

This advanced water purifier comes with a number of tailor-made Quick Fit tap adapters, to help you having an easy and simple installation of your purifier in your tap. Real sense and simplicity.

Hi-flow

This counter-top water purifier has a maximum flow rate of 4 liters per minute, which gives you excellent performance comparable to the normal flow rate of your unfiltered water. By simply rotating the nozzle, you have a choice of a stream or a spray of filtered water. At your kitchen tap, you can also select either stream or spray tap water by turning the water selection lever. Pure water made easy, at your kitchen.

360° rotation arm

The 360° rotation arm on the counter top can be easily stored away when not in use to provide you maximum working space in your kitchen. When the rotation arm is fully swung out, it reaches over your kitchen sink like a separate tap. The swivel nozzle gives you the ultimate control in direction of water flow. MAximum convenience for you and your family

Specifications

General specifications

Accessories: 8 QuickFit tap-mounting adapters, 9 QuickFit tap-mounting adapters
Replacement filter cartridge: HD3902
Water selection: filtered spray, filtered stream, unfiltered spray, unfiltered stream

Design specifications

Product weight: 1.4 kg
Product dimensions (L x W x H): 112 x 140 x 240 mm

Purification system

Chlorine reduction capacity: 8000 liters
Turbidity reduction: 4000 liters

Filter specifications

Filter lifetime: 3000 liters or approx. 1 year
Major filter components: granular activated carbon - GAC, granular activated coral, hollow-fiber membrane

Water input conditions

Input water flow: 4 liters/min, water pressure @ 100kPa, water temperature @ 20°C
Max. input water temperature: 35 °C

