

PHILIPS

Toaster oven

45 min timer

temperature control

Black



HD4496



Delicious hot food easily

45 minutes timer

The multi-purpose toaster oven that does almost anything! Bakes, broils, toasts and warms, with lots of easy-cook features for delicious results every time.

Ideal for cooking different snacks

- Bakes, broils, toasts, warms food and snacks
- Adjustable temperature control for optimal result
- Large baking tray for cooking different foods
- 900-1000W high power

Simple design with clear indication

- On/off light shows status clearly
- Ready bell sounds when food is ready

The ultimate in convenience

- 45-minute timer shuts off the oven once ready
- Detachable rack for easy handling
- Non stick coating tray for easy cleaning

Highlights

Bakes & toast food

Good for toasting , browning/crisping, defrosting, grilling and baking different food.

Adjustable temperature control

80-230C adjustable, use the temperature selector to set the required cooking temperature.

Large baking tray

Capacity: 9L; can grill chicken meat or to defrost mini-pizzas

900-1000W high power

Good for cooking different food

On/off light



Clearly indicate the status

Ready bell sounds

Clearly indicate the cooking status.

45-minute timer

Easy to preset cooking and ready on time.

Detachable rack

Convenient and safe to handle different cooking.

Non stick coating tray

Durable and easy to clean

Specifications

General specifications

Temperature control

Baking tray

On/off light

Ready bell

Detachable rack

Non stick tray

9L capacity

Design specifications

Available color(s): Black

Color(s): Black

Product dimensions (L x W x H): 30 x 36.3 x 17.0 cm

Technical specifications

Power: 1000W (HK, Malaysia, Singapore), 900 W

Capacity: 9 l

Voltage: 220 V

Frequency: 50/60 Hz

Cord length: 0.9 m

Accessories included

Baking tray: 245.5 (L) x 208.5 (W) x 20.8 (H) mm