

PHILIPS

Rice cooker

Daily Collection

1.0 liter

600W

HD4513/60



Great tasting rice, just as you remember it

Smart program brings out the great taste of rice

Powered by Philips innovative FragrantTaste Technology, with its automatic optimum controlled heating temperatures at each stage of the cooking process, every grain of rice is well cooked to shiny fluffy fragrant taste

Smart and automatic cooking

- Automatic keep warm keeps rice fresh for 12 hours
- 24-hour preset timer ensures rice and meal ready on time
- Easy to control cooking progress
- 10 Multifunction programs for a variety of dishes

Quick and easy

- "Tornado Cooking" accelerates the cooking time just 25 min
- Easy-to-read water level indicator

Every grain well cooked

- 5-layer Crystal Black Pot for even heating
- Fragrant Retention Valve to lock original tasty Rice
- "FragrantTaste" enhances optimal moisture absorption
- Controls temperature accuracy at every stage of cooking

Highlights

Automatic 12 hours keep warm

Use the keep warm function to keep rice warm for a longer period of time. When the cooking process is finished, the rice cooker automatically switches to the keepwarm mode

24-Hour preset time



24-hour preset timer ensures rice and meal ready on time.

25-minutes "Tornado cooking"



The rice is cooked at high power and regulated by a microcontroller chip, which accelerates the cooking time so you can cook delicious rice with ease in just 25 minutes, saving 1/3 cooking time.

5-layer Crystal Black Pot



5-layer non-stick and anti-scratch coating ensures inner pot is long lasting and easy to clean.

Fragrant Retention Valve



The water content of the rice is locked in via the unique steam return loop design, retaining the original fragrance of the rice.

FragrantTaste Technology



Enhance moisture absorption for firm yet shiny fluffy rice. Controls temperature accuracy at every stage of cooking to optimize the taste.

Large digital display

Large digital display makes it easy to control cooking progress.

Multifunction programs



10 menus, including: Standard cook, Quick cook, Porridge, Grains, Small portion, Clay pot rice, Soup, Cake, Noodles and Reheat.

Temperature control

Controls temperature accuracy at every stage of cooking

Water level indicator

Easy-to-read water level indicator

Specifications

Design specifications

Materials of main body: Plastic

Dimensions (L x W x H): 365*274*224 mm

Color(s): White and Orange

Accessories

Measuring cup

2-in-1 rice spoon

Technical specifications

Voltage: 220-240 V

Frequency: 50/60 Hz

Wattage: 600 W

Cord length: 1.20 m

Capacity: 1 L

