

PHILIPS

Fuzzy Logic Rice Cooker

Daily Collection

3.0mm ultra thick inner pot

Digital display

1.8L



HD4515/63



Enjoy the goodness of multigrain

Cook rice and grain easier in thick non-stick pot

3.0mm ultra thick inner pot enhances thermal conductivity and heat-retaining greatly, so heat-transmit is constantly strong and even during cooking to ensure every grain of rice and multigrains are well cooked.

Ultra thick inner pot

- 3.0mm ultra thick enhances thermal conductivity greatly
- Constant strong heat to cook tasty rice and multigrain
- 5 layers inner pot with durable non-stick coating

Multiple functions

- 8 dedicated cooking menus for the contemporary cook
- 12 hours keep warm

Ease of use

- Detachable inner lid for easy cleaning
- Large digital display provides easy-to-read menus and time

Highlights

3.0mm thick inner pot



3.0mm ultra thick inner pot with superior heat conductivity to cook great tasty rice and multigrain.

Constant heat

Ultra thick inner pot ensures constant strong heat to cook tasty rice and multigrain.

5 layers



5 layers inner pot with durable non-stick coating.

8 menus



8 multifunction programs with separate menus for rice, multigrain and beans for a variety of dishes.

12 hours keep warm




Keep the food warm and fresh for up to 12 hours.

Detachable inner lid



Detachable inner lid for easy cleaning.

Large digital display



Large digital display provides easy-to-read menus and time for easy operation.

Specifications

Accessories

Included: Measuring cup, Spatula, Steaming tray/basket

General specifications

Product features: Detachable vent, On/off switch, Preset cooking function, Time control, Power-on light

Prefix programs: 8

Type of lid: Fixed

Keep warm function: 12 hour(s)

Technical specifications

Cord length: 1.0 m

Frequency: 50/60 Hz

Voltage: 220~240 V

Power: 790~940 W

Design

Color of control panel: Dark beluga

Color: White

Finishing

Material of main body: Plastic

Service

2-year worldwide guarantee

Country of origin

Made in: China

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

