

PHILIPS

IH Rice Cooker

Avance Collection

iSpiral IH technology

Bakuhanseki coating iron pot

1.5L



HD4528/62



Tasty multigrain with every grain well cooked With the innovative iSpiral IH technology

Patented iSpiral IH technology stepping out of traditional IH thanks to our leading IH structure and micro processor form ultra strong outside-in currents that enables every grain well cooked.

iSpiral IH technology

- Create strong outside-in waterflow to heat grains evenly
- Strong power distribution to ensure well-cooked grains

Bakuhanseki coating iron pot

- Bakuhanseki coating contains minerals and trace elements
- 5-layer iron pot with superior heat conductivity and durable

Multiple functions

- 10 dedicated cooking menus for the contemporary cook
- 12 hours keep warm

Ease of use

- Detachable inner lid for easy cleaning
- Large digital display provides easy-to-read menus and time

Highlights

iSpiral IH technology



Patented iSpiral induction heating technology to create strong vortex which can make sure every grain is heated evenly and well cooked.

Power distribution

Strong power distribution due to iSpiral IH technology to ensure every grain is well cooked.

Bakuhanseki coating iron pot

Bakuhanseki coating contains minerals and trace elements which are all essential to a healthy human body; 5-layer iron pot with superior heat conductivity and durable.

5-layer iron pot

5-layer iron pot with superior heat conductivity and durable

10 menus



10 multifunction programs with separate menus for rice, multigrain and beans for a variety of dishes.

12 hours keep warm




Keep the food warm and fresh for up to 12 hours.

Detachable inner lid

Detachable inner lid for easy cleaning.

Large digital display



Large digital display provides easy-to-read menus and time for easy operation.

Specifications

Accessories

Included: Measuring cup, Spatula, Steaming tray/basket

General specifications

Product features: Detachable vent, On/off switch, Preset cooking function, Time control, Power-on light

Keep warm function: 12 hour(s)

Prefix programs: 10

Type of lid: Fixed

Technical specifications

Cord length: 1.0 m

Frequency: 50/60 Hz

Voltage: 220~240 V

Power: 1500 W

Design

Color of control panel: Dark beluga

Color: Black

Finishing

Material of main body: Plastic

Service

2-year worldwide guarantee

Country of origin

Made in: China

Sustainability

Packaging: > 90% recycled materials

User manual: 100% recycled paper

