

# PHILIPS

## mini kettle

Daily Collection

0.8 L 900 W

1 cup indicator

white



HD4609/00



## Boil just what you need

### Save up to 50% energy

The unique "one cup indicator" feature of this mini kettle allows you to boil only the water you need, without taking up too much space in your kitchen. Therefore, you can easily save up to 50% energy and reduce your impact on environment

#### Boil what you need

- One cup indicator to boil only the water you need

#### Easy to experience

- Hinged lid with large opening for easy filling and cleaning
- Easy to read water level indicators on both sides
- Light indicates when the kettle is switched on
- Cord winder for easy storage
- Cordless 360° pirouette base for easy lifting and placing

#### Fast boiling and easy cleaning

- Flat heating element for fast boiling and easy cleaning
- Anti-calc filter for a clean cup of water

#### Safe to use


- Four-way safety system



asimpleswitch.com

# Highlights

## One cup indicator



Enabling consumers to boil the amount of water they need, and therefore saving of up to 50% energy and water, contributing to a better environment.

## Pilot light



Elegant blue light incorporated in the on/off switch indicates when the kettle is on.


## Hinged lid



Hinged lid with large opening for easy filling and cleaning, also avoiding steam contact.



## Flat heating element



The stainless steel concealed element ensures fast boiling and easy cleaning.

## Anti-calc filter



Anti-calc filter for a clean cup of water and a cleaner kettle.

## Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

# Specifications

## Design specifications

**Color(s):** bright white

**Materials:** Heating element: Stainless steel, Housing: Polypropylene/ ABS, Switch & toolholder: Polypropylene

## General specifications

**Cordless**

**Non slip feet**

**Ergonomic grip**

**Easy spout filling**

**Wide opening lid**

**Cord storage**

**Automatic shut-off**

**Boil-dry protection**

**360 degrees base**

**Lid as well as spout filling**

**Flat heating element**

## Technical specifications

**Capacity:** 0.8 l

**Power:** 900 W

**Cord length:** 0.75 m

**Voltage:** 220-240 V

**Frequency:** 50-60 Hz

## Dimensions

**Product dimensions (WxDxH):**

15.8x18.5x22 cm

**Packaging dimensions (WxDxH):**

22.5x22.5x22.5 cm

## Service

**2-year worldwide guarantee**

