

PHILIPS

Kettle

1.7 L 2400 W

1 cup indicator

Gloss metal

Hinged lid



HD4654/20



Boil just what you need

Save up to 66% energy

The unique "one cup indicator" feature of this stylish designed metal kettle allows you to boil only the water you need. Therefore, you can easily save up to 66% energy and reduce your impact on environment.

Boil what you need

- One cup indicator to boil only the water you need

Easy to experience

- Easy lid and spout filling
- Hinged lid with large opening for easy filling and cleaning
- Easy to read water level indicator
- Light indicates when the kettle is switched on
- Power cord winder for easy storage
- Cordless 360° pirouette base for easy lifting and placing

Fast boiling and easy cleaning

- Flat heating element for fast boiling and easy cleaning
- Robust metal kettle with brushed stainless steel body
- Anti-calc filter for a clean cup of water

Safe to use

- Multi safety system

Highlights

One cup indicator



Enabling consumers to boil the amount of water they need, and therefore saving of up to 66% energy and water, contributing to a better environment.

Pilot light



Elegant blue light incorporated in the on/off switch indicates when the kettle is on.


Easy lid and spout filling



The kettle can be filled via the spout or by opening the lid.



Flat heating element



The stainless steel concealed element ensures fast boiling and easy cleaning.

Anti-calc filter



Anti-calc filter for a clean cup of water and a cleaner kettle.

Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

Specifications

General specifications

Product features: 360 degrees base, Automatic shut-off, Boil-dry protection, Cord storage, Flat heating element, Non-slip feet

Technical specifications

Power: 2400 W

Cord length: 0.75 m

Voltage: 220-240 V

Frequency: 50-60 Hz

Capacity bowl: 1.7 L

Service

2-year worldwide guarantee

Design and finishing

Color(s): Gloss metal - black

Material heating element: Stainless steel

Material of main body: Stainless steel

Material switch: Polypropylene (PP)

Weight and dimensions

Dimensions of packaging (LxWxH):

190x244x278 mm

Dimensions of product (LxWxH):

248x163x235 mm

