

# PHILIPS

## Kettle

1.7 l 3000 W

1 cup ind.

brushed metal



HD4671/20



## Boil just what you need

### Save up to 66% energy

The unique "one cup indicator" feature of this stylishly designed metal kettle allows you to boil only the water you need. Therefore, you can easily save up to 66% energy and reduce your impact on the environment

#### Boil what you need

- One cup indicator to boil only the water you need

#### Easy to experience

- Spring lid with large opening for easy filling and cleaning
- Easy to read water level indicators on both sides
- Light indicates when the kettle is switched on
- Cord winder for easy storage
- Cordless 360° pirouette base for easy lifting and placing

#### Fast boiling and easy cleaning

- Flat heating element for fast boiling and easy cleaning
- Robust metal kettle with brushed stainless steel finishing
- Anti-calc filter for a clean cup of water

#### Safe to use

- Cool wall for a safe touch
- Four-way safety system



[asimpleswitch.com](http://asimpleswitch.com)



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## One cup indicator



Enabling consumers to boil only the amount of water they need, and therefore saving up to 66% energy and water, contributing to a better environment.

## Pilot light



Elegant blue light incorporated in the on/off switch indicates when the kettle is on.

## Spring lid



Spring lid with large opening for easy filling and cleaning, also avoiding contact with steam.



## Flat heating element



The stainless steel concealed element ensures fast boiling and easy cleaning.

## Anti-calc filter



Anti-calc filter for a clean cup of water and a cleaner kettle.

## Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

# Specifications

## Design specifications

Colour(s): brushed metal - black

Materials: Heating element: Stainless steel,  
Housing: Stainless steel and PP, Switch and  
tool holder: Polypropylene

## General specifications

Cordless

Non-slip feet

Ergonomic grip

Easy spout filling

Wide opening lid

Cord storage

Automatic shut-off

Boil-dry protection

360-degree base

Lid as well as spout filling

Flat heating element

## Technical specifications

Capacity: 1.7 l

Power: 2500-3000 W

Cord length: 0.75 m

Voltage: 220-240 V

Frequency: 50-60 Hz

## Dimensions

Product dimensions (WxDxH): 16.2 x 27.2 x  
24.7 cm

Packaging dimensions (WxDxH):  
27.4x18.5x27.8 cm

## Service

2-year worldwide guarantee



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.