

# PHILIPS

## Kettle

1.7 l 3000 W

1 cup indicator

brushed metal



HD4671/60



## Boil just what you need

### Save up to 66% energy

The unique "one cup indicator" feature of this stylishly designed metal kettle allows you to boil only the water you need. Therefore, you can easily save up to 66% energy and reduce your impact on the environment

#### Boil what you need

- One cup indicator to boil only the water you need

#### Easy to experience

- Easy to read water level indicators on both sides
- Power cord winder for easy storage
- Cordless 360° pirouette base for easy lifting and placing
- Pilot light indicates when the kettle is switched on
- Spring lid with large opening for easy filling and cleaning

#### Fast boiling and easy cleaning

- Robust metal kettle with brushed stainless steel finishing
- Flat heating element for fast boiling and easy cleaning
- Anti-calc filter for a clean cup of water

#### Safe to use

- Multi safety system
- Lid knob stays cool for a safe touch



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## One cup indicator

Enabling consumers to boil only the amount of water they need, and therefore saving up to 66% energy and water, contributing to a better environment.

## Stainless steel finishing

Robust metal kettle with brushed stainless steel finishing

## Water level indicators

Easy-to-read water level indicators on both sides of the Philips electric kettle for left- and right-handed use.

## Power cord winder



The cord can be wrapped around the base, so that the kettle is easy to place in your kitchen.

## Multi safety system

Multi safety system against boil-dry, with auto switch-off when ready or when lifted from the base.

## Cordless 360° pirouette base



Cordless 360° pirouette base for easy lifting and placing.

## Flat heating element

The stainless steel concealed element ensures fast boiling and easy cleaning.

## Pilot light

Elegant light incorporated in the on/off switch indicates when the kettle is on.

## Anti-calc filter

Anti-calc filter for a clean cup of water and a cleaner kettle.

## Spring lid

Spring lid with large opening for easy filling and cleaning, also avoiding contact with steam.

## Lid knob stays cool

Lid knob stays cool for a safe touch.

# Specifications

## Design specifications

**Colour(s):** brushed metal - black

**Materials:** Heating element: Stainless steel, Housing: Stainless steel and PP, Switch and tool holder: Polypropylene

## General specifications

**Cordless**

**Non-slip feet**

**Ergonomic grip**

**Easy spout filling**

**Wide opening lid**

**Cord storage**

**Automatic shut-off**

**Boil-dry protection**

**360-degree base**

**Lid as well as spout filling**

**Flat heating element**

## Technical specifications

**Capacity:** 1.7 l

**Power:** 2500-3000 W

**Cord length:** 0.75 m

**Voltage:** 220-240 V

**Frequency:** 50-60 Hz

## Dimensions

**Product dimensions (WxDxH):** 16.2 x 27.2 x 24.7 cm

**Packaging dimensions (WxDxH):**

27.4x18.5x27.8 cm

## Service

**2-year worldwide guarantee**

