

PHILIPS


coolwall



Let's make things better.



PHILIPS




HD 4820

toastissimo

Coolwall 2-slot toaster with electronically controlled browning and removable crumbtray.

coolwall



FEATURES


- Coolwall
- Removable crumbtray
- Cancel function integrated in the browning control (position 0)
- Cord storage
- Electronic timer - 7 positions and temperature control
- Micanite elements and well-balanced toastchamber

BENEFITS

Pleasant and safe-to-touch
 Easy cleaning, collects bread crumbs
 Greater safety and convenience

Easy storage of the appliance
 Consistent browning

Perfect even browning



TECHNICAL DATA


Power consumption / Voltage
 Cord length (free length)
 Product dimensions (LxWxH)
 Slot dimensions (LxWxD)
 Heating elements

800 Watt / 220 - 240 V
 1.10 m
 260 x 150 x 180 mm (incl. crumbtray)
 130 x 20 x 120 mm
 Flat winded micanite heating elements

MATERIAL / COLOURS

Top Housing
 Bottom
 Sliding knob / Browning knob
 Top plate
 Cord set (Standard Euro-version)
 Handgrip crumbtray

Polypropylene	Ivory
Polypropylene	Ivory
Polycarbonate	Amber
Chrome-plated steel	—
PVC H03VV	Ivory
Polycarbonate	Amber



PACKAGING

Dimensions F-Box (LxWxH)
 Weight F-Box
 Dimensions A-box (LxWxH)
 Weight A-box
 Products per A-box
 Pallet quantity

313 x 178 x 205 mm
 1.6 kg
 554 x 328 x 428 mm
 10.7 kg
 6 pcs
 144 pcs

EAN - CTV

EAN code F-box / A-box
 CTV code appliance

8710103 078463 / 8710103 078470
 8824 820 00000