

PHILIPS

Coffee maker

Café Gourmet

With glass jug

Boil and brew system

Magic Purple

HD5407/40



The plate you can put your cups on with the Philips Café Gourmet coffee maker

The Philips Café Gourmet coffee machine ensures optimal coffee extraction, for a rich aroma and full flavor, thanks to the high brewing temperature of the unique Boil & Brew system, reaching 93°C or higher.

Great taste and aroma

- Boil & Brew system for ultimate aroma and taste
- Maintain the hot coffee temperature after brewing
- Aroma twister circulates the coffee for an optimal taste

Easy to experience

- Drip stop to pour a cup of coffee whenever you like
- Swing filter holder for easy filling of coffee
- Cable storage for easy placement in your kitchen
- Dishwasher-safe parts for easy cleaning

Highlights

Aroma twister



This smart nozzle inside the jug circulates the inflowing coffee evenly through the jug for an optimal and consistent aroma, from the first to the last cup.

Boil & Brew



The Philips coffeemaker has a unique Boil & Brew system. Water is boiled first and then flows through ground coffee. Thanks to high brewing temperature reaching 93°C or higher, this ensures the richest flavor and superior aroma for your filter coffee.

Keep your coffee hot



After brewing your coffee, the heating plate maintains the coffee temperature, for hot and tasty coffee.

Drip stop




The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

Cable storage




Spare cable can be stored in the cable compartment under the coffee maker. It enables placing the coffee maker nicely in your kitchen.

Swing filter holder



The filter holder is opened by swinging it to the side, which makes the filling of coffee easy. The filter holder is also detachable, for easy cleaning.

Dishwasher-safe parts



The jug and filter holder can be easily cleaned in the dishwasher.

Specifications

General specifications

Coffee drinks: Drip filter coffee

Suitable for: Ground coffee powder

Ease of cleaning & maintenance: Dishwasher-safe parts, Removable filter holder

Ease of use and comfort: Drip stop, Translucent water tank, Water level indication

Accessories

Included: Glass jug

Technical specifications

Voltage: 220-240 V

Frequency: 50-60 Hz

Brewing time for a jug: 10 min

Capacity water tank: 1 L

Capacity water tank: Up to 10 cups

Cord length: 0.8 m

Finishing

Material of main body: Polypropylene

Material water tank: Glass

Sustainability

Power consumption brewing: 1300 W

Weight and dimensions

Dimensions of packaging (WxDxH): 240 x 240 x 569 mm

Dimensions of product (WxDxH): 195 x 225 x 510 mm

Weight of product: 2.3 kg

Design

Color: Magic purple

