

PHILIPS

Coffee maker

Café Gourmet

With glass jug

Boil and brew system

Stainless Steel



HD5412/00



The taste of handmade filter coffee, since 1988 with the Philips Café Gourmet coffee maker

The Philips Café Gourmet coffee machine ensures optimal coffee extraction, for a rich aroma and full flavor, thanks to the high brewing temperature of the unique Boil & Brew system, reaching 93°C or higher.

Great taste and aroma

- Aroma twister circulates the coffee for an optimal taste
- Boil & Brew system for ultimate aroma and taste
- Maintain the hot coffee temperature after brewing

Easy to experience

- Drip stop to pour a cup of coffee whenever you like
- Swing filter holder for easy filling of coffee
- Cable storage for easy placement in your kitchen
- Auto shut-off after 30 min. for energy saving and safety
- Dishwasher-safe parts for easy cleaning

Highlights

Aroma twister



This smart nozzle inside the jug circulates the inflowing coffee evenly through the jug for an optimal and consistent aroma, from the first to the last cup.

Boil & Brew



The Philips coffeemaker has a unique Boil & Brew system. Water is boiled first and then flows through ground coffee. Thanks to high brewing temperature reaching 93°C or higher, this ensures the richest flavor and superior aroma for your filter coffee.

Keep your coffee hot



After brewing your coffee, the heating plate maintains the coffee temperature, for hot and tasty coffee.

Drip stop




The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

Automatic shut-off (30 min)



30 Minutes after brewing your coffee, the coffeemaker switches off automatically for energy saving and safety. This is according to EU regulation, which is applicable for all coffee makers in the EU. If you want your coffee to stay hot longer, Philips offers coffee makers with a thermal jug.

Swing filter holder




The filter holder is opened by swinging it to the side, which makes the filling of coffee easy. The filter holder is also detachable, for easy cleaning.

Cable storage



Spare cable can be stored in the cable compartment under the coffee maker. It enables placing the coffee maker nicely in your kitchen.

Dishwasher-safe parts



The jug and filter holder can be easily cleaned in the dishwasher.

Specifications

Service

2-year guarantee

Sustainability

Power consumption brewing: 1300 W

Finishing

Material water tank: Glass

Material of main body: Stainless steel & plastic

Accessories

Included: Glass jug

General specifications

Coffee drinks: Drip filter coffee

Suitable for: Ground coffee powder

Special functions: Boil & brew

Ease of use and comfort: Translucent water tank, Automatic shut-off, Drip stop, Water level indication

Ease of cleaning & maintenance: Removable filter holder, Dishwasher-safe parts

Technical specifications

Water boilers: 0

Brewing time for a jug: 10 min

Capacity water tank: 1 L

Cord length: 0.8 m

Voltage: 220 - 240 V

Frequency: 50 - 60 Hz

Capacity water tank: Up to 12 cups

Design

Color: Black & Metal

Weight and dimensions

Dimensions of product (WxDxH): 195 x 225 x 510 mm

Weight of product: 2.3 kg

Dimensions of packaging (WxDxH): 240 x 240 x 569 mm

Country of origin

Made in: Poland

