

# PHILIPS

Super-automatic  
espresso machine

HD5720/30



## Smile with every cup of coffee

### Push once for your perfect espresso

Philips' one-touch espresso maker, with a full 15 bar of pressure, gives you delicious espresso at the push of a button. Beans are ground freshly by the automatic grinder. And the stainless-steel finishing makes for an eye-catching design.

#### **Tasty cappuccino**

- Patented steam pipe for better, easier frothing
- Separate boilers for steam and coffee making
- Fast: direct steam for milk frothing

#### **Delicious results**

- 15-bar high-pressure brewing: great aroma and crema layer
- Fully automatic system guarantees consistent taste
- Professional-quality automatic mill to grind fresh beans
- Pre-brewing for flavor enhancing
- Stainless-steel cup warmer, so drinks stay warm longer
- Lots of choice: espresso, cappuccino, café crème and more

#### **Self-explanatory display**

- Easily adjustable settings (volume, strength, temperature)
- Preferred settings can be saved

#### **Total convenience**

# Highlights

## Patented steam pipe



Patented steam pipe for better, easier frothing

## 15-bar, high-pressure brewing



15-bar high-pressure brewing: great aroma and crema layer

## Fully automatic



Fully automatic system guarantees consistent taste

## Professional-quality automatic grinder



Professional-quality automatic mill to grind fresh beans

## Cup warmer



Stainless-steel cup warmer, so drinks stay warm longer

## Lots of choice



Lots of choice: espresso, cappuccino, café crème and more

## Easily adjustable settings



Easily adjustable settings (volume, strength, temperature)

## Easily accessible water tank



Easily accessible water tank on the front

## Automatic cleaning and descaling programs



Automatic cleaning and descaling programs

## Hot water dispenser



Hot water dispenser for hot beverages

# Specifications

## Technical specifications

**Boiler Thermoblock:** 2x, stainless-steel

**Power:** 1350 W

**Pressure:** 15 bar

**Water tank:** 1.7 L

**Coffee bean container:** 220 g

**Grinder fineness settings:** 13

## Design and finishing

**Housing:** Brushed stainless-steel, Anti finger print and easy-to-clean coating

## Country of origin

Made in: Italy

