

# PHILIPS

Super-automatic  
espresso machine

HD5730/10



## So simple, so delicious

Push once for your perfect cappuccino or macchiato

Philips' premium one-touch espresso maker gives you delicious cappuccino at the push of a button: milk is frothed and added to your coffee automatically. And the sleek, stainless-steel design means the machine looks great from any angle.

### Easy cappuccino

- Push once for a delicious cappuccino or latte macchiato
- Automatic milk frothing in unique milk container
- Fast: milk and espresso are prepared in parallel

### Unique milk container

- Easy storage in refrigerator door
- Dishwasher-safe
- AutoClean button for instant cleaning

### Delicious results

- 15-bar high-pressure brewing: great aroma and crema layer
- Fully automatic system guarantees consistent taste
- Professional-quality automatic mill to grind fresh beans

### Self-explanatory display

### Total convenience

# Highlights

## Easy cappuccino

Philips' new one-touch espresso maker gives you delicious espresso variations, like cappuccino and latte macchiato, at the push of a button. Beans are ground freshly each time by the automatic grinder. Then, milk is frothed and added to your coffee automatically, so you never have to jiggle the jug under the steam spout. What's more, the unique milk container clicks easily onto the machine, fits perfectly in the fridge and can even be cleaned in the dishwasher. Simply push once and enjoy your favourite espresso variations at home in a matter of moments.

## Automatic milk frothing

Automatic milk frothing in unique milk container

## Refrigerator door storage

Easy storage in refrigerator door

## Dishwasher-safe

Dishwasher-safe

## Auto Clean button for instant cleaning

AutoClean button for instant cleaning

## 15-bar, high-pressure brewing

15-bar high-pressure brewing: great aroma and crema layer

## Fully automatic

Fully automatic system guarantees consistent taste

## Professional-quality automatic grinder

Professional-quality automatic mill to grind fresh beans

## Cup warmer

Stainless-steel cup warmer, so drinks stay warm longer

## Lots of choice

Lots of choice: espresso, cappuccino, café crème and more

## Easily adjustable settings

Easily adjustable settings (volume, strength, temperature)

## Easily accessible water tank

Easily accessible water tank on the front

## Automatic cleaning and descaling programs

Automatic cleaning and descaling programs

## Hot water dispenser

Hot water dispenser for hot beverages

# Specifications

## Technical specifications

**Boiler Thermoblock:** 2x, stainless-steel

**Power:** 1350 W

**Pressure:** 15 bar

**Water tank:** 1.7 L

**Coffee bean container:** 220 g

**Grinder fineness settings:** 13

## Design and finishing

**Housing:** Anti finger print and easy-to-clean coating, Brushed stainless-steel and aluminium

## Country of origin

**Made in:** Italy

