

Frying range 2001



HD 6162



HD 6160



HD 6134



HD 6132



HD 6130

FRYERS

	Metal HD 6162 Semi Professional Cool Zone	HD 6160 Semi Professional Cool Zone	Cucina HD 6134¹ Cool Wall Cool Zone	HD 6132² Cool Wall Cool Zone	HD 6130³ Cool Wall Cool Zone
Technical Data					
Power (W)	2200	2200	2200	2200	1600 (HD 6130) 2000 (HD 6140)
Voltage (V)	220 - 240	220 - 240	220 - 240	220 - 240	220 - 240
Oil capacity (L) (max)	4,0	4,0	3,5	3,5	2,5
Basket capacity (g) (max)	1300	1300	1250 (HD 6144)	1250 (HD 6142)	1000 (HD 6140)
Shape	oval	oval	square	square	square
Housing material	stainless steel	coated steel	polypropylene	polypropylene	polypropylene
Colour / Graphics	lilac/charcoal grey	white/mineral green	ivory/blue	ivory/blue	ivory/blue
Cord length (m)	1,20	1,20	1,20	1,20	1,20
Dimensions (mm) (HxWxD)	280x250x420	280x250x420	255x300x380	255x300x380	235x300x380
Weight (incl. packaging) (Kg)	4,7	4,7	4,8	4,7	4,5
Features					
Adjustable thermostat	●	●	●	●	●
Temperature pilot lamp	●	●	●	●	●
Cool Wall	-	-	●	●	●
Cool Zone	●	●	●	●	●
Lid					
- hinged	-	-	●	●	●
- removable	●	●	●	●	●
- dishwasher proof	●	●	●	●	●
Automatic lid release	-	-	●	●	●
Filter					
- permanent (metal)	-	-	●	●	●
- polyester/carbon	-	-	-	-	-
Viewing window	-	-	●	●	●
Basket handle					
- detachable	-	-	-	-	-
- collapsible	●	●	-	-	-
- rise and fall mechanism	-	-	●	●	●
Basket with drip-out position	●	●	●	●	●
Timer	-	-	●	-	-
Inner pot					
- fixed/ oil pour-out facility	-	-	-	-	-
- removable	●	●	●	●	●
- dishwasher proof	●	-	●	●	●
- non-stick coated	-	-	● (HD 6144)	● (HD 6142)	● (HD 6140)
- stainless steel	●	●	● (HD 6134)	● (HD 6132)	● (HD 6130)
- brushed aluminium	-	-	-	-	-
Interior cord storage	●	●	●	●	●
Non slip feet	●	●	●	●	●
On/off switch	●	●	●	●	●
Auto off (120 min)	-	-	●	-	-

1) Sept. 2001: HD 6144

2) Sept. 2001: HD 6142

3) Sept. 2001: HD 6140



PHILIPS

Let's make things better.



HD 6124



HD 6122



HD 6120



HD 6110/13



HD 4292



HD 4283



HD 4282



HD 4432

FRYERS

	Comfort Plus HD 6124 Cool Wall	HD 6122 Cool Wall	HD 6120 Cool Wall	Comfort HD 6110/13 Cool Wall Intro sept. 2001	Compact HD 4292 Cool Wall	Economy HD 4283	HD 4282
Technical Data							
Power (W)	1900	1900	1900	1900	1300	1900	1900
Voltage (V)	220 - 240	220 - 240	220 - 240	220 - 240	220 - 240	220 - 240	220 - 240
Oil capacity (L) (max)	2,3	2,3	2,3	2,0	1.7 - 2.0	2,0	2,0
Basket capacity (g) (max)	1200	1200	1200	1000	1000	1000	1000
Shape	square	square	square	round	square	round	round
Housing material	polypropylene	polypropylene	polypropylene	polypropylene	polypropylene	coated steel	coated steel
Colour / Graphics	white/mineral green	white/mineral green	white/mineral green	white/mineral green	ivory/orange	white/mineral green	white/mineral green
Cord length (m)	1,20	1,20	1,20	1,20	1,30	1,00	1,00
Dimensions (mm) (HxWxD)	250x300x360	250x300x360	250x300x360	253xø324(excl. handles)	244x240x280	277xø256	275xø256(excl. handles)
Weight (incl. packaging) (Kg)	4,3	4,3	4,3	2,5	3,5	2,5	2,3
Features							
Adjustable thermostat	●	●	●	●	●	●	●
Temperature pilot lamp	●	●	●	●	●	●	●
Cool Wall	●	●	●	●	●	-	-
Cool Zone	-	-	-	-	-	-	-
Lid							
- hinged	●	●	●	●	●	●	-
- removable	●	●	●	●	●	●	●
- dishwasher proof	●	●	●	●	●	-	-
Automatic lid release	●	●	●	●	●	●	-
Filter							
- permanent (metal)	●	●	●	●	●	-	-
- polyester/carbon	-	-	-	-	-	●	●
Viewing window	●	●	●	-	●	-	-
Basket handle							
- detachable	-	-	-	-	-	●	●
- collapsible	-	-	-	●	●	-	-
- rise and fall mechanism	●	●	●	-	-	-	-
Basket with drip-out position	●	●	●	●	●	●	●
Timer	●	-	-	● (HD 6113 only)	-	-	-
Inner pot							
- fixed/ oil pour-out facility	●	●	●	●	●	●	●
- removable	-	-	-	-	-	-	-
- dishwasher proof	-	-	-	-	-	-	-
- non-stick coated	●	●	-	-	●	-	-
- stainless steel	-	-	-	-	-	-	-
- brushed aluminium	-	-	●	●	-	●	●
Interior cord storage	●	●	●	●	●	●	●
Non slip feet	●	●	●	●	●	●	●
On/off switch	●	-	-	-	-	-	-
Auto off (120 min)	●	-	-	-	-	-	-

Contact Grill

	Metal HD 4432
Technical Data	
Power (W)	1600
Voltage (V)	120, 220 - 240
Shape	square
Housing material	lacquered steel plate
Colour / Graphics	lilac/charcoal grey
Cord length (m)	1,40
Dimensions (mm) (HxWxD)	130x382x335
Weight (incl. packaging) (Kg)	3,9
Features	
Adjustable thermostat	●
Pilot lamp	●
Grill plates	
- aluminium	●
- non-stick coated (double layer)	●
- removable	●
- dishwasher proof	●
Grilling positions	
- contact	●
- gratin	●
- sandwich	●
- party grill	●
Cool touch handles	●
Juice drainage channel	●
Cord storage	●