

# PHILIPS

## Table grill

Daily Collection

1500 W

Duo Plate: Ribbed/Smooth plate

420 X 240 mm

HD6320/20



## Flip the plate to grill your way

### Duo grill: smooth and ribbed plates

Philips table grill with duo plate. The smooth surface is ideal for gently cooking food like vegetables, fish and shrimp; ribbed surface for grilling pieces of meat like steak, hamburgers or sausages with irresistible grilling stripes.

#### **Provides me tastier grilled food**

- Duo plate to choose smooth or ribbed grilling
- Non-stick plate to grill without adding any oil
- Adjustable thermostat ensures perfect results for every food

#### **Makes grilling indoors a comfortable experience**

- Integrated grease tray to collect the excess fat
- Sloped grill to drain excess fat away
- Detachable dishwasher-safe plate for easy cleaning

# Highlights

## Duo plate



The duo plate is reversible and therefore lets you cook with either a ribbed or smooth grilling surface, so that you can enjoy your food exactly the way you like. The smooth plate is suitable for cooking small pieces of food. The ribbed surfaces create that irresistible flame-grilled effect on your pieces of meat.

## Grease tray



Excess grease is drained to dishwasher safe grease tray

## Non-stick grilling plate



Non-stick surfaces allow you to cook without any added oil, so you only taste the flavour of food

## Sloped grill body



Sloped grill makes the excess fat flow into grease tray therefore decreases the smell and smoke

## Adjustable thermostat



Wide temperature range (70°C to 230°C) to choose the ideal temperature for each ingredient so that you ensure the perfect results for every food

## Dishwasher-safe grilling plate



Dishwasher-safe plate, which is detachable, enables easy cleaning

# Specifications

## General specifications

Non-slip feet  
Temperature light

## Weight and dimensions

Weight appliance: 3 kg  
Product dimensions (W x H x D): 420 X 100 X 240 mm  
Grill plate dimensions (W x D): 420 X 240 mm

## Technical specifications

Power: 1500 W

## Design and finishing

Materials: Plastic  
Color(s): Black

