



**SENSEO® Viva Café**  
Coffee pod machine

- SENSEO coffee boost technology
- Crema plus technology
- Intensity Select
- Star White



HD6563/01

Discover a more intense coffee experience  
with Crema plus, coffee boost and intensity select

Crema plus ensures the finest and most velvety crema layer. While the Coffee boost technology disperses the water through the coffee pad, via 45 holes, for richer flavors. With a simple double press, you can also brew strong short coffees.

**Enjoy the best tasting SENSEO® coffee**

- Crema Plus for a finer and more velvety crema layer
- Coffee Boost gets the most out of your SENSEO® coffee pad
- Machine is tested >10.000 times to ensure consistent quality

**Coffee variety for every moment**

- Intensity Select for a long-smooth or a short-strong coffee
- Vast variety of SENSEO® coffee blends and flavors

**Premium design**

- Adjust the coffee spout to fit your favorite cup or mug
- Real metal drip tray

**Fast and easy operation**

- The only coffee pod maker that brews two cups at a time
- Direct Start makes your coffee when the machine is heated up
- 30-minute auto shut-off for energy saving and safety
- The decalcifying light reminds you when to descale



*Senseo®*

**PHILIPS**

\* Based on retail sales volumes

# Highlights

## Crema plus technology



Crema Plus technology ensures the finest and most velvety crema layer. For each SENSEO® cup of coffee.

## Adjustable real metal spout



Adjust the spout's position to fit your favorite cup or mug

## Automatic shut-off



The SENSEO® coffee maker automatically shuts off after 30 minutes after making coffee, for energy cost saving and appliance safety.

## Coffee Boost technology



Coffee Boost technology disperses the hot water, via 45 aroma nozzles, evenly through each SENSEO® coffee pad. Get the most out of your coffee pad for the best tasting SENSEO® coffee.

## 1 or 2 cups at the same time



Prepare 1 or 2 cups of your delicious SENSEO® coffee in less than a minute.

## Variety of blends and flavors



SENSEO® has a vast variety of different coffee blends and flavors. Each blend has its own distinctive taste to fit your personal preference.

## Intensity Select



Double-click the 1 or 2 cup button for a short-strong SENSEO® coffee.

## Decalcification indicator



The SENSEO® coffee maker reminds you when to descale. Descale with SENSEO® Descale every 3 months to keep your appliance lime scale free; ensuring: maximal in-cup volume; perfect coffee temperature, and; the appliance's durability. Do not use vinegar, since it might damage your SENSEO® appliance and affects the coffee taste.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Design

- Color: Star White

## Finishing

- Material drip tray: Metal
- Material of spout: Stainless steel

## Country of origin

- Made in: Poland

## General specifications

- Suitable for: SENSEO® Coffee pods
- Cups at the same time: 2
- Ease of cleaning & maintenance: Descale indicator, Dishwasher-safe parts
- Ease of use and comfort: Removable spout, Removable water tank, Automatic shut-off, Brew stop, Direct start
- Coffee drinks: Café Crème
- SENSEO coffee boost technology

## Sustainability

- Power consumption brewing: 1450 W
- Power consumption stand-by: 0.36 W
- Made of recycled materials: 90% (paperwork and

packaging)

## Service

- 2-year guarantee

## Technical specifications

- Capacity water tank: 0.9 L
- Capacity water tank: Up to 6 cups
- Cord length: 0.8 m
- Frequency: 50 Hz
- Max. cup height: 100 - 120 mm
- Pump pressure: 1 bar
- Voltage: 220-240 V
- Water boilers: 1
- Brewing time one cup: 30 sec
- Brewing time two cups: <60 sec

## Weight and dimensions

- Dimensions of packaging (WxDxH): 232 x 370 x 380 mm
- Dimensions of product (WxDxH): 190 x 310 x 340 mm
- Weight incl. packaging: 2.4 kg
- Weight of product: 1.75 kg

