

SENSEO®
Espresso podholder

• for SENSEO® coffee machines

HD7003/10



Sensational freshly brewed espresso coffee!

Espresso Coffee Pod holder for SENSEO®

More variety from SENSEO®: Enjoy a delicious small cup of high-quality strong and intense SENSEO® Espresso coffee — freshly brewed by your SENSEO® coffee machine.

Ultimate convenience

- Improved pod holder design for easier coffee pod placement

Sensational coffee

- Delicious coffee foam layer for your special coffee moment
- Delicious coffee foam layer for your special coffee moment
- Unique brewing system for optimal taste



* Based on retail sales volumes

Senseo

PHILIPS

Espresso podholder
for SENSEO® coffee machines

HD7003/10

Specifications

Technical specifications

- Only suitable for: HD7824, HD7841, HD7842, HD7850, HD7852, HD7820, HD7822, HD7823, HD7830, HD7860, HD7825, HD7827, HD7835, HD7826, HD7828, HD7833, HD7855, HD7856, HD7857, HD7863, HD7864, HD7880, HD7884

Country of origin

- Made in: Poland

Weight and dimensions

- Product dimensions (L x D x H): 157 x 85 x 49 mm
- Product weight: 0.1 kg

Highlights

Delicious coffee foam layer



The fine Douwe Egberts SENSEO® coffee selection and the unique SENSEO® brewing system make sure that your perfect cup of coffee always comes with a rich and delicious coffee foam layer - proof of premium taste and quality.

Issue date 2019-03-06

© 2019 Koninklijke Philips N.V.
All Rights reserved.

Version: 5.0.1

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

12 NC: 0000 000 00000

www.philips.com