

PHILIPS

Teamaker

0.7 L 1650 W

Personal settings

Wood brown/white cream

Large tea filter

HD7311



Bring your tea to life

Naturally brewed to enjoy the goodness and flavor

The intelligent Philips tea maker helps release the aromas out of each tea. By combining a specially designed teapot, a natural, convenient brewing process and tea of the best quality, you can enjoy a unique taste experience, every time.

Specially designed for tea

- Large tea filter for optimal aroma
- Double walled pot keeps the tea warm
- Clean stainless steel materials for filter and pot

Getting all the goodness

- Optimal temperature and brew time
- Quick-select buttons for popular tea types
- Personal settings for more tea variety
- Special light ring feature

Suitable for all your tea

- Any loose leaf tea or teabag

Highlights

Large tea filter



The large filter and round shape of the Philips tea maker allow the aroma of the tea to fully develop.

Double walled pot



The double walled pot of the tea maker keeps the tea warm for you.

Stainless steel materials



Even the most subtle aromas are being revealed, because only carefully selected materials are used, which are also easy to clean.

Quick-select buttons



Four Quick-select buttons make it easy to prepare the most popular types of tea, including the black, green, rooibos and fruit herbal tea. Just choose the tea you would like to drink to prepare it with the optimal temperature and brewing time.

Personal settings



With the personal setting you can always choose your own temperature and brewing time. Adjustable temperature: 60-100°C
Adjustable brewing time: 1-10 min

Special light ring feature



After placing the filter the light ring gradually fills up until the optimal brewing time is reached and the leaves can be removed. So you never have to be late anymore to remove your tea leaves.

Any loose leaf tea or teabag



You can use any of your own teas. The tea maker is optimal for loose leaf tea, but you can also use tea bags.

Specifications

Design specifications

Materials: Stainless steel

Color(s): Wood brown and white cream

Technical specifications

Capacity: 0.7 L

Power: 1385-1650 W

Voltage: 220-240 V

Frequency: 50 Hz

Dimensions

Product dimensions (WxDxH):

19.5x19.5x23 cm

Packaging dimensions (WxDxH):

36.5x20.5x23.5 cm

Service

2-year worldwide guarantee

