



Philips
Coffee maker

1.3 l 900 W



HD7446/00

Good Coffee Easily

Holds 10 to 15 cups, compact design

Easy-to-use and reliable coffee maker with a smart and compact design for easy storage.

Easy to experience

- Translucent water tank shows the water level in the tank
- Dishwasher-proof parts for easy cleaning
- The drip stop prevents dripping coffee on the hotplate
- Detachable swing filter

Compact Design

- 1.3 l for 10-15 cups
- Cord storage

PHILIPS
sense and simplicity

Specifications

General specifications

- Translucent water tank
- Dishwasher-proof swing filter & jug
- Drip stop
- Detachable swing filter
- Cord storage
- Non-slip feet

Technical Specifications

- Power: 900 W
- Capacity: 1.3 / 10-15 Litres/cups
- Voltage: 220-240 V
- Frequency: 50/60 Hz

- Cord length: 0.88 m
- Brewing time: 11 minute(s)

Design specifications

- Colour: White
- Bowl, cover, pusher: Plastic (polypropylene), Glass jug
- Dimensions (L x W x H): 220 x 220 x 290 mm
- Weight (incl. Packaging): 1.94 kg
- Weight of the appliance: 1.42 kg

Accessories

- Jug: HD7983/70 (White)



Issue date 2009-06-10

Version: 2.1

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com