

# PHILIPS

Coffee maker

Daily Collection

With glass jug

Black

HD7447/20



## Simply good coffee

With aroma twister for the best taste experience

Enjoy good coffee with a reliable coffeemaker in a smart and compact design for easy storage

### Great taste and aroma

- Aroma twister circulates the coffee for an optimal taste

### Easy to experience

- Smart water level indication
- Drip stop to pour a cup of coffee whenever you like
- LED power switch
- Dishwasher-safe parts for easy cleaning

### Compact design

- 1.2 L capacity for 10 - 15 cups

## Highlights

### Smart water level indication



This smart water level indicator is integrated into the water tank, allowing you to follow easily how many cups you filled.

### Drip stop




The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

### 1.2 L for 10 - 15 cups




The jug of this coffeemaker will fit 1.2 L coffee, enough for 10 to 15 cups, depending on your cup size.

### LED power switch




Light indicates that the Philips coffee machine is switched on.

### Dishwasher-safe parts



The glass jug and filter holder can be easily cleaned in the dishwasher.

### Aroma twister



This smart nozzle inside the jug circulates the inflowing coffee evenly through the jug for an optimal and consistent aroma, from the first to the last cup.

## Specifications

### Accessories

Included: Glass jug

### Design

Color: Black

### General specifications

#### Ease of cleaning & maintenance:

Dishwasher-safe parts, Removable filter holder

**Coffee drinks:** Drip filter coffee

**Compatible coffee serving:** Ground coffee powder

**Ease of use and comfort:** Drip stop, Water level indication

### Technical specifications

**Frequency:** 50/60 Hz

**Voltage:** 220-240 V

**Brewing time for a jug:** 10 min

**Capacity water tank:** 1.2 L

**Cord length:** 0.85 m

### Weight and dimensions

**Dimensions of product (WxDxH):** 220 x 220 x 290 mm

**Weight of product:** 1.42 kg

### Country of origin

Made in: China

### Finishing

**Material of main body:** Plastic

**Material water tank:** Plastic

