

# PHILIPS

Coffee maker

Daily Collection

With thermal jug

Black & metal

HD7478/20



## Simply good coffee

### Unbreakable stainless steel thermal jug

Enjoy good coffee with a reliable coffeemaker in a smart and compact design for easy storage

#### **Great taste and aroma**

- Stainless steel thermal jug to keep temperature for long
- Water level indication for easy filling

#### **Designed around you**


- Compact size for saving space in your kitchen

#### **Easy to experience**

- Drip stop to pour a cup of coffee whenever you like
- Direct automatic shut-off for energy saving and safety
- LED power switch lights up when the coffee maker is switched


## Highlights

### Drip stop



The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

### Direct automatic shut-off



## Auto-off

After brewing your coffee, the coffeemaker switches off automatically for energy saving and safety. The thermal jug will ensure that the coffee stays hot.

## Specifications

### Accessories

Included: Unbreakable thermal jug

### Design

Color: Black

### Sustainability

Power consumption brewing: 1000 W

### Weight and dimensions

Weight of product: 1.42 kg

Weight incl. packaging: 1.94 kg

Dimensions of product (WxDxH): 220 x 220 x 290 mm

### Finishing

Material of main body: Stainless steel & plastic

Material water tank: Plastic

### Country of origin

Made in: China

### Service

2-year guarantee

### General specifications

Suitable for: Ground coffee powder

Special functions: IntensBrew

Ease of use and comfort: Water level indication, Drip stop

Ease of cleaning & maintenance:

Dishwasher-safe parts, Removable filter holder

Coffee drinks: Drip filter coffee

### Technical specifications

Pump pressure: No pump

Water boilers: 0

Brewing time for a jug: 10 min

Cord length: 0.85 m

Capacity water tank: 1 L

Voltage: 220 - 240 V

Frequency: 50 - 60 Hz

