

PHILIPS

Coffee maker

Glass

Aroma Swirl

Lilac

HD7562/35



Great coffee till the last drop

Aroma Swirl circulates coffee for optimal blend

This elegant coffee maker allows you to enjoy a rich aroma thanks to the Aroma Swirl. A smart nozzle in your coffee pot circulates your coffee for an optimal spread of aroma throughout the whole jug

Enjoy a rich aroma

- Aroma Swirl circulates coffee for optimal spread of aroma
- High speed pump ensures optimal aroma
- Aroma jug to optimally preserve the coffee flavour

Experience simplicity

- Protective buffer ring to protect jug from breaking
- Illuminated power switch
- Dishwasher proof parts
- Translucent water tank shows the water level in the tank
- Detachable swing filter
- Easy storage of redundant cord length
- Drip stop to interrupt the brewing whenever you want

Highlights

Aroma Swirl

Smart nozzle circulates coffee for optimal spread of aroma.

High speed brewing

High speed pump ensures optimal aroma.

Protective buffer ring

Protective buffer ring to protect jug from breaking.

Illuminated power switch

Light indicates that the Philips coffee machine is switched on.

Aroma jug

Aroma jug to optimally preserve the coffee flavour.

Water level indication

Translucent water tank shows the water level in the tank.

Detachable swing filter

Detachable swing filter for easy filling and cleaning.

Cord storage



Easy storage of redundant cord length

Drip stop



Drip stop to interrupt brewing whenever you want to pour a cup of coffee

Specifications

Design specifications

Weight of the appliance: 1.6 kg

Dimensions (L x W x H): 223 x 256 x 358 mm

Materials: Polypropylene/Glass jug

Colour(s): Lilac

Weight (incl. packaging): 2.1 kg

General specifications

Cord storage

Non-slip feet

Translucent water tank

Illuminated power switch

Detachable swing filter

Drip-stop

Dishwasher proof parts

Aroma jug

Accessories

Aroma jug

Technical specifications

Power: 1000 W

Voltage: 220–240 V

Frequency: 50/60 Hz

Cord length: 0.85 m

Capacity: 1.2/10-15 Litres/cups

Brewing time: < 10 minute(s)