

PHILIPS

Coffee maker

Glass

Aroma Swirl

Black

HD7563/20



Great coffee till the last drop

Aroma Swirl circulates coffee for optimal blend

This elegant coffee maker allows you to enjoy a rich aroma thanks to the Aroma Swirl. A smart nozzle in your coffee pot circulates your coffee for an optimal spread of aroma throughout the whole jug

Enjoy a rich aroma

- Aroma Swirl circulates coffee for optimal spread of aroma
- High speed pump ensures optimal aroma
- Aroma jug to optimally preserve the coffee flavour

Experience simplicity

- Drip stop to interrupt the brewing whenever you like
- Illuminated power switch
- Dishwasher proof parts
- Detachable swing filter
- Translucent water tank shows the water level in the tank
- Easy storage of redundant cord length

Highlights

Aroma Swirl

Smart nozzle circulates coffee for optimal spread of aroma.

High speed brewing

High speed pump ensures optimal aroma.

Drip stop

The Philips coffee machine has drip stop to interrupt the brewing whenever you like.

Illuminated power switch

Light indicates that the Philips coffee machine is switched on.

Aroma jug

Aroma jug to optimally preserve the coffee flavour.

Detachable swing filter

Detachable swing filter for easy filling and cleaning.

Water level indication

Translucent water tank shows the water level in the tank.

Cord storage

Easy storage of redundant cord length.

Specifications

Design specifications

Weight of the appliance: 1.6 kg

Materials: Polypropylene/Glass jug

Dimensions (L x W x H): 223 x 256 x 358 mm

Colour(s): Black

Weight (incl. packaging): 2.1 kg

General specifications

Cord storage

Non-slip feet

Translucent water tank

Illuminated power switch

Detachable swing filter

Drip-stop

Dishwasher proof parts

Aroma jug

Accessories

Aroma jug

Technical specifications

Power: 1000 W

Voltage: 220-240 V

Frequency: 50/60 Hz

Cord length: 0.85 m

Capacity: 1.2/10-15 Litres/cups

Brewing time: < 10 minute(s)

