

PHILIPS


Coffee maker

Café Gaia

With glass jug

Black & metal

HD7564/20



Delicious & hot coffee, in our iconic design Aroma twister for optimal taste in each cup

The Café Gaia coffee maker brings excellent quality, in both coffee quality as in design. The aroma twister circulates the coffee through the jug for an optimal taste in each cup of coffee.

Great taste and aroma


- Aroma twister circulates the coffee for an optimal taste
- A rich coffee flavor due to a concentrated waterflow

Easy to experience

- Water level indication for easy filling
- Swing filter holder for easy filling of coffee
- Cable storage compartment for easy placement in your kitchen
- Drip stop to pour a cup of coffee whenever you like
- Dishwasher-safe parts for easy cleaning

Highlights

Aroma twister



This smart nozzle inside the jug circulates the inflowing coffee evenly through the jug for an optimal and consistent aroma, from the first to the last cup.

Rich coffee flavor




Thanks to the concentrated water flow that is poured onto the coffee bed, optimal flavors are extracted from the coffee grounds.

Drip stop



The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

Swing filter holder



The filter holder is opened by swinging it to the side, which makes the filling of coffee easy. The filter holder is also detachable, for easy cleaning.

Cable storage compartment




Spare cable can be stored very easily in the cable compartment in the back of the coffee maker. It enables placing the coffee maker nicely in your kitchen.

Water level indication



Fill the water tank easily and precisely with the water level indication.

Dishwasher-safe parts



The jug and filter holder can be easily cleaned in the dishwasher.

Specifications

Accessories

Included: Glass jug

Design

Color: Black & Metal

Finishing

Material of main body: Stainless steel & plastic

Material water tank: Plastic

Country of origin

Made in: Poland

General specifications

Suitable for: Ground coffee powder

Ease of cleaning & maintenance: Dishwasher-safe parts, Removable filter holder

Ease of use and comfort: Water level indication, Drip stop

Coffee drinks: Drip filter coffee

Service

2-year guarantee

Sustainability

Power consumption brewing: 1000 W

Technical specifications

Capacity water tank: 1.2 L

Capacity water tank: Up to 15 cups

Cord length: 0.85 m

Frequency: 50 - 60 Hz

Voltage: 220 - 240 V

Water boilers: 0

Brewing time for a jug: 10 min

Weight and dimensions

Dimensions of product (WxDxH):
230x215x335 mm

Weight incl. packaging: 4 kg

Weight of product: 1.7 kg

