

PHILIPS

Coffee maker

Café Gaia

With glass jug

Black



HD7567/20



Delicious & hot coffee, in our iconic design

Aroma twister for optimal taste in each cup of coffee

The Café Gaia coffee maker brings excellent quality, in both coffee quality as in design. The aroma twister circulates the coffee through the jug for an optimal taste in each cup of coffee.

Great taste and aroma

- Aroma twister circulates the coffee for an optimal taste
- A rich coffee flavor due to a concentrated waterflow

Easy to experience

- Swing filter holder for easy filling of coffee
- Auto shut-off after 30 min. for energy saving and safety
- Cable storage compartment for easy placement in your kitchen
- Drip stop to pour a cup of coffee whenever you like
- Dishwasher-safe parts for easy cleaning
- Timer to wake up with the smell of fresh coffee
- Water level indication for easy filling

Highlights


Automatic shut-off (30 min)



Auto-off

30 Minutes after brewing your coffee, the coffeemaker switches off automatically for energy saving and safety. This is according to EU regulation, which is applicable for all coffee makers in the EU. If you want your coffee to stay hot longer, Philips offers coffee makers with a thermal jug.

Aroma twister



This smart nozzle inside the jug circulates the inflowing coffee evenly through the jug for an optimal and consistent aroma, from the first to the last cup.

Rich coffee flavor




Thanks to the concentrated water flow that is poured onto the coffee bed, optimal flavors are extracted from the coffee grounds.

Drip stop



The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

Swing filter holder



The filter holder is opened by swinging it to the side, which makes the filling of coffee easy. The filter holder is also detachable, for easy cleaning.

Cable storage compartment



Spare cable can be stored very easily in the cable compartment in the back of the coffee maker. It enables placing the coffee maker nicely in your kitchen.

Dishwasher-safe parts



The jug and filter holder can be easily cleaned in the dishwasher.

Timer



Wake up with the smell of fresh coffee thanks to the timer. Prepare your coffee maker, set the time, and a fresh jug of coffee is brewed at the time you desire.

Water level indication



Fill the water tank easily and precisely with the water level indication.

Specifications

Finishing

Material water tank: Plastic
Material of main body: Plastic

Service

2-year guarantee

Accessories

Included: Glass jug

Design

Color: Black, Black & Metal

Country of origin

Made in: Poland

General specifications

Type of display: LCD
Suitable for: Ground coffee powder
Ease of cleaning & maintenance: Dishwasher-safe parts, Removable filter holder
Ease of use and comfort: Automatic shut-off, Display, Water level indication, Drip stop
Coffee drinks: Drip filter coffee
Special functions: Aroma twister

Sustainability

Power consumption brewing: 1000 W

Technical specifications

Water boilers: 0
Capacity water tank: 1.2 L
Capacity water tank: Up to 15 cups
Cord length: 0.85 m
Frequency: 50 - 60 Hz
Voltage: 220 - 240 V
Brewing time for a jug: 10 min

Weight and dimensions

Dimensions of product (WxDxH):
230x215x335 mm
Weight incl. packaging: 3.7 kg
Weight of product: 1.6 kg

