

PHILIPS

Coffee maker

Café Gaia

With glass jug

Black



HD7567/20



Delicious hot coffee, in our iconic design

Aroma twister for optimal taste in each cup of coffee

The Café Gaia coffee maker brings excellent quality, both in coffee quality and in design. The aroma twister circulates the coffee through the jug for an optimal taste in each cup of coffee.

Great taste and aroma

- Aroma twister circulates the coffee for optimal taste
- A rich coffee flavour due to a concentrated water flow

Easy to experience

- Swing filter holder for easy filling of coffee
- Auto shut-off after 30 min. for energy-saving and safety reasons
- Cable storage compartment for easy placement in your kitchen
- Drip stop to pour a cup of coffee whenever you like
- Dishwasher proof parts for easy cleaning
- Timer to wake up with the smell of fresh coffee
- Water level indication for easy filling

Highlights

Aroma twister



This smart nozzle inside the jug circulates the inflowing coffee evenly through the jug for an optimal and consistent aroma, from the first to the last cup.

Automatic shut-off (30 min)



Auto-off

30 minutes after brewing your coffee, the coffee maker switches off automatically to save energy and for safety. This is in accordance with EU regulations, which apply to all coffee makers in the EU. If you want your coffee to stay hot longer, Philips offers coffee makers with a thermal jug.

Rich coffee flavour




Thanks to the concentrated water flow that is poured onto the coffee bed, optimal flavours are extracted from the coffee grounds.

Drip stop




The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

Swing filter holder



The filter holder is opened by swinging it to the side, which makes it easy to fill up with coffee. The filter holder is also detachable for easy cleaning.

Cable storage compartment



Spare cable can be stored very easily in the cable compartment at the back of the coffee maker. This means that the coffee maker can be positioned nicely in your kitchen.

Dishwasher-safe parts



The glass jug and filter holder can easily be cleaned in the dishwasher.

Timer



Wake up to the smell of fresh coffee thanks to the timer. Prepare your coffee maker, set the time and a fresh jug of coffee is brewed at the time you choose.

Water level indication



Fill the water tank easily and precisely with the water level indication.

Specifications

Finishing

Material water tank: Plastic
Material of main body: Plastic

Service

2 year guarantee

Accessories

Included: Glass jug

Design

Colour: Black, Black and Metal

Country of origin

Made in: Poland

General specifications

Type of display: LCD
Suitable for: Ground coffee powder
Ease of cleaning and maintenance:
Dishwasher-safe parts, Removable filter holder
Ease of use and comfort: Automatic shut-off,
Display, Water level indication, Drip stop
Coffee drinks: Drip filter coffee
Special functions: AromaSwirl

Sustainability

Power consumption brewing: 1000 W

Technical specifications

Water boilers: 0
Capacity water tank: 1.2 l
Capacity water tank: Up to 15 cups
Cord length: 0.85 m
Frequency: 50 - 60 Hz
Voltage: 220 - 240 V
Brewing time for a jug: 10 min

Weight and dimensions

Dimensions of product (W x D x H): 230 x 215
x 335 mm
Weight incl. packaging: 3.7 kg
Weight of product: 1.6 kg

