

PHILIPS

Coffee maker


Viva Collection

With glass jug

Aroma Swirl with timer

White

HD7567/70



Great coffee till the last drop

Aroma Swirl circulates coffee for optimal blend

This elegant Philips coffee maker allows you to enjoy a rich drip coffee aroma thanks to the Aroma Swirl. A smart nozzle in your coffee pot circulates your filter coffee for an optimal spread of aroma through the whole coffee jug.

Great taste and aroma

- A rich coffee flavor due to a concentrated waterflow
- Aroma jug preserves the coffee flavor

Easy to experience

- Buffer ring for protection and stability
- Drip stop to pour a cup of coffee whenever you like
- Water level indication for easy filling
- Swing filter holder for easy filling of coffee
- Cable storage for easy placement in your kitchen
- Dishwasher-safe parts for easy cleaning
- Timer to wake up with the smell of fresh coffee
- 1.000 Watt
- Auto shut-off after 2 hours

Highlights

Auto shut-off



Forgot to turn off the coffee machine? Don't worry! 2 hours after brewing the coffee, the coffee machine will shut off automatically to save energy.

Protective buffer ring



The buffer ring around the glass jug provides protection and improved stability.

1.000 Watt



The pump of your Philips coffee machine will prepare your coffee quickly.

Glass aroma jug




The Philips Aroma jug is made of glass and designed to optimally preserve the coffee flavor.

Cable storage



Spare cable can be stored in the cable compartment under the coffee maker. It enables placing the coffee maker nicely in your kitchen.

Swing filter holder



The filter holder is opened by swinging it to the side, which makes the filling of coffee easy. The filter holder is also detachable, for easy cleaning.

Drip stop



The drip stop allows you to pour a cup of coffee before the full brewing cycle is finished.

Water level indication



Fill the water tank easily and precisely with the water level indication.

Dishwasher-safe parts



The jug and filter holder can be easily cleaned in the dishwasher.

Timer



Wake up with the smell of fresh coffee thanks to the timer. Prepare your coffee maker, set the time, and a fresh jug of coffee is brewed at the time you desire.

Rich coffee flavor



Thanks to the concentrated water flow that is poured onto the coffee bed, optimal flavors are extracted from the coffee grounds.

Specifications

Accessories

Included: Glass jug

Design

Color: White

Finishing

Material of main body: Plastic

Country of origin

Made in: Poland

General specifications

Suitable for: Ground coffee powder

Ease of cleaning & maintenance: Dishwasher-safe parts, Removable filter holder

Ease of use and comfort: Translucent water tank, Water level indication, Drip stop, Preset timer

Coffee drinks: Drip filter coffee

Sustainability

Power consumption brewing: 1000 W

Technical specifications

Capacity water tank: 1.2 L

Capacity water tank: Up to 15 cups

Cord length: 0.85 m

Frequency: 50/60 Hz

Voltage: 220-240 V

Brewing time for a jug: 10 min

Weight and dimensions

Dimensions of product (WxDxH):

230x215x335 mm

Weight of product: 1.6 kg

